

60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz

PE70A6000



Features

- Non-Reflective 10 Bit Programmable 60 dB Pin Diode Attenuator
- 0.5 GHz to 18 GHz Frequency Range
- 60 dB Attenuation Range
- Step Resolution of 0.06 dB
- 1 Watt Average Survival Power
- Insertion Loss 4.5 dB Max
- VSWR 2.0:1 Max
- RF Connectors are SMA Female
- 15 Pin Micro-D Female Connector

Applications

- Electronic Warfare
- Test & Measurement
- Military & Space
- Radar
- Military Communications Systems

Description

The PE70A6000 is a Non-Reflective 10 Bit Programmable 60 dB Pin Diode Attenuator with Step Resolution as Low as 0.06 dB over the Operating Frequency Range from 0.5 GHz to 18 GHz. The PE70A6000 is offered in a slim line housing measuring only 0.5" Height. The RF Input/Output Connectors are SMA Female. Along with a 15 Pin Micro-D Female Control Socket. The unit is shipped with a Micro-D Mating Connector.

Electrical Specifications (Values at +25°C, sea level)

Description	Min	Typ	Max	Unit
Frequency Range	0.5		18	GHz
Impedance		50		Ohms
Attenuation Range	0		60	dB
Insertion Loss			4.5	dB
VSWR			2:1	
Power Rating		15	30	dBm
Survial Power Average -40 to +85 deg C			+30	dBm
Attenuation Flatness				
@ 10 dB		±1		dB
@ 20 dB		±1		dB
@ 40 dB		±1.25		dB
@ 60 dB		±3		dB
Accuracy of Attenuation				
0 dB to 20 dB		±1		dB
20 dB to 40 dB		±1.5		dB
40 dB to 60 dB		±2		dB
Step Size	0.06			dB
Switching Time			1	
Off Time			0.5	us
DC Voltage		±12	15	Volts
DC Current			150	mA

60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz

PE70A6000



Electrical Specifications (Values at +25°C, sea level)

Description	Min	Typ	Max	Unit
Logic Input "0" (Bit Off)	-0.3		0.8	Volts
Logic Input "1" (Bit On)	2		5	Volts

Mechanical Specifications

Size

Length	2 in [50.8 mm]
Width	1.8 in [45.72 mm]
Height	0.5 in [12.7 mm]
Weight	0.148 lbs [67.13 g]
Connector 1	SMA Female
Connector 2	SMA Female

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-65 to +125 deg C
Humidity	MIL-STD-202F, METHOD 103B COND. B
Shock	MIL-STD-202F, METHOD 213B COND. B
Vibration	MIL-STD-202F, METHOD 204D COND. B
Altitude	MIL-STD-202F, METHOD 105C COND. B
Temperature Cycle	MIL-STD-202F, METHOD 107
Salt Spray	MIL-STD-202F, METHOD 105C COND. B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:


- Values at 25 °C, sea level
- ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

60 dB With 10 Bit Programmable TTL Controlled
Attenuator, SMA Female To SMA Female,
0.06 dB Steps From 500 MHz To 18 GHz



PE70A6000

Typical Performance Data



60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz



PE70A6000

Insertion Loss and VSWR @ 0dB Attenuation



20dB Attenuation



60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz

PE70A6000



40dB Attenuation



60dB Attenuation




60 dB With 10 Bit Programmable TTL Controlled
Attenuator, SMA Female To SMA Female,
0.06 dB Steps From 500 MHz To 18 GHz

PE70A6000




Delay On
Measured with a Tunnel Diode @ 10GHz
Power Level +5dBm



Channel 1 (Yellow): Tunnel Diode output
Channel 2 (Green): TTL Input from Signal Generator

Delay Off
Measured with a Tunnel Diode @ 10GHz
Power Level +5dBm



Channel 1 (Yellow): Tunnel Diode output
Channel 2 (Green): TTL Input from Signal Generator

60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz

PE70A6000



60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz PE70A6000](#)

URL: <https://www.pasternack.com/60db-programmable-sma-female-sma-female-0-watts-attenuator-pe70a6000-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE70A6000 CAD Drawing

60 dB With 10 Bit Programmable TTL Controlled Attenuator, SMA Female To SMA Female, 0.06 dB Steps From 500 MHz To 18 GHz

