



SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off
Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

Electromechanical Relay Switches Technical Data Sheet

PE71S6534

Features

- SP4T Electromechanical Relay Switch
- IP64 Level 1 Rated
- DC to 26.5 GHz Frequency Range
- Latching Self Cut-Off Actuator
- 5M Lifecycle Rating
- +COM
- Suppression Diodes
- Insertion Loss 0.3 dB typ
- Isolation > 70 dB typ
- VSWR as low as 1.25:1 max
- SMA Female Connectors
- +28 Volt DC Bias
- 15 Pin D-Sub Connector for DC Control
- -54°C to +85°C Operating Temperature
- Up to 90 Watt Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions
- Actuating Set/Reset Feature

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Description

The PE71S6534 is a Ruggedized SP6T electromechanical relay switch that operates across a broadband frequency range from DC to 26.5 GHz and can handle up to 90W of average power in a break before make condition. The 50 Ohm design is IP64 compliant with a Level 1 moisture seal and specifically designed to operate reliably in harsh usage environments and conditions, such as over extreme temperatures and wet or dusty environments. Intrusion protection offers full protection against dust and other particulates. Moisture protection enables resistance to splashes in all directions. The switch has a Latching Self Cut-Off Actuator that magnetically latches in place after the control voltage is removed. DC Current is required to change positions. For power sensitive applications, this is the best actuator option. Additional features include positive common (+COM) configuration, and suppression diodes which limit voltage spikes or reverse current. Impressive typical performance includes 0.3 dB insertion loss and isolation greater than 70 dB. This switch requires +28Vdc bias voltage, operates over a temperature range of -54°C to +85°C, and is rated for 5 million lifecycles. The rugged and compact package assembly supports SMA female connectors and a 15 pin D-Sub connector for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = 25°C, DC Voltage = 28 Vdc)

Switch Type	SP6T
Actuator Type	Latching
Actuator Options	Diodes, Self Cut Off, + COM

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		26.5	GHz
Impedance		50		Ohms
Operating Voltage	26	28	30	Volts
Actuating Set Current			110	mA

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA PE71S6534](#)



SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6534

Actuating Reset Current		660	mA
VSWR	1.3:1	1.8:1	
Insertion Loss	0.3	0.8	dB
Isolation	50	90	dB
Switching Time	<20		ms Typ

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12	12 to 18	18 to 26.5		GHz
VSWR, Max	1.25:1	1.4:1	1.5:1	1.8:1		
Insertion Loss, Max	0.2	0.4	0.5	0.8		dB
Isolation, Min	70	60	60	50		dB

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width/Diameter	1.75 in [44.45 mm]
Height	1.75 in [44.45 mm]
Weight	0.188 lbs [85.28 g]

Connectors

RF Connector Type	SMA Female
Control Connector	D-Subminiature

Environmental Specifications

Temperature

Operating Range	-54 to +85 deg C
Storage Range	-55 to +100 deg C

Ingress Protection (IP) Rating
Shock

IP64
MIL-STD-202 Method 213, Condition D, 500 G (non oper)

Vibration

MIL-STD-202 Method 204, Condition D, 10G RMS (non oper)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA PE71S6534](#)




SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off
Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6534

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA PE71S6534](#)



SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off
Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6534



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA PE71S6534](#)





SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6534

Power Handling vs. Frequency



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA PE71S6534](#)



SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6534

SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA PE71S6534](https://www.pasternack.com/sp6t-electromechanical-relay-latching-switch-26.5-ghz-diodes-com-sma-pe71s6534-p.aspx)

URL: <https://www.pasternack.com/sp6t-electromechanical-relay-latching-switch-26.5-ghz-diodes-com-sma-pe71s6534-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S6534 CAD Drawing

SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch, +COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA

F E D C B A

F E D C B A

1

2

3





4

5

6

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	02/06/2023	DMAY	TGALLA

REVISION	



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
.XX = ±.02 [.5] ±.1/32
.XXX = ±.005 [.13] ANGLES ± 1°
CABLE LENGTH TOLERANCES:
≤ 12 [305] = ±.1 [25] / -0
> 12 [305] ≤ 60 [1524] = +.2 [51] / -0
> 60 [1524] ≤ 120 [3048] = +.4 [102] / -0
> 120 [3048] ≤ 300 [7620] = +.6 [152] / -0
> 300 [7620] = +.5% / -0

NOTES:
1. LABEL PER ILS-100-02, FOR INTERNAL REFERENCE ONLY.
LABEL LOCATION FOR REFERENCE ONLY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

SP6T, SMA, LATCHING, SCO, +COM, 26.5GHz, 28VDC, DIODES,
D-SUB, RUGGEDIZED




INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE NONE
SHEET 1 OF 2

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	DMAY	PE71S6534	A

T-Rev.D2

SP6T, IP64 Rated Electromechanical Relay Latching Self Cut-Off Switch,
+COM, DC to 26.5 GHz, Diodes, 90W, 28VDC, SMA




TRUTH TABLE/PIN ASSIGNMENT:
PIN ASSIGNMENT

TERMINALS D-SUB PIN ASSIGNMENT	RF PATH					
	J1	J2	J3	J4	J5	J6
1 (SET-)	ON	OFF	OFF	OFF	OFF	OFF
2 (SET-)	OFF	ON	OFF	OFF	OFF	OFF
3 (SET-)	OFF	OFF	ON	OFF	OFF	OFF
4 (SET-)	OFF	OFF	OFF	ON	OFF	OFF
5 (SET-)	OFF	OFF	OFF	OFF	ON	OFF
6 (SET-)	OFF	OFF	OFF	OFF	OFF	ON
14 (RESET-)	OFF	OFF	OFF	OFF	OFF	ON
ALL OFF						

PIN 15, +COM

SCHEMATIC

(COIL 1 SHOWN LAST ENERGIZED)



- ACTUATION CHARACTERISTICS:
- REQUIRES TWO (2) SEQUENTIAL PULSES (RESET & SET)
- T1 & T2 = 30mSEC MIN
- T3 = 10mSEC MIN
- T4 & T5 = 20mSEC MAX

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [.5] FRACTIONS
.XX = ±.02 [.5] ±.132
.XXX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = ±2 [51] / -0
>60 [1524] ≤ 120 [3048] = ±4 [102] / -0
>120 [3048] ≤ 300 [7620] = ±6 [152] / -0
>300 [7620] = ±5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

SP6T, SMA, LATCHING, SCO, +COM, 26.5GHz, 28VDC, DIODES,
D-SUB, RUGGEDIZED

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	DMAY	PE71S6534	A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.