

Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control



PE70A2000

Features

- Analog Controlled 60 dB Pin Diode Attenuator
- 2 GHz to 4 GHz Frequency Range
- Insertion Loss 2.0 dB Max
- VSWR 2.0:1 Max
- Input Power 20 dBm Operating
- Input Power 30 dBm Survival
- Switching Time 500 nsec
- Removable SMA Female Connectors
- 15 Pin Micro D Control Connector

Applications

- Electronic Warfare
- Test & Measurement
- Military & Space
- Radar
- Military Communications Systems

Description

The PE70A2000 is an Analog Controlled 60 dB Pin Diode Attenuator operating from 2 GHz to 4 GHz, and over a temperature range of -55 Deg C to + 85 Deg C. The Input/Output RF Connectors are Removable SMA Female. The control connector is a 15 Pin Micro D, with a mating connector supplied.

Electrical Specifications (Values at +25°C, sea level)

Description	Minimum	Typical	Maximum	Units
Frequency Range	2		4	GHz
Attenuation Range	0		60	dB
			2	dB
VSWR			2:1	
RF Input Power		+20		dBm
Survival Power Rating			+30	dBm
		±0.45		dB
		±0.8		dB
		±1.5		dB
		±1.6		dB
Switching Time			500	ns
Switching Speed			500	ns
Analog Control		10		dB/Volt
Control Voltage	0		6	Volts
DC Power Supply				
12 to 15 VDC			125	mA
-12 to -15 VDC			50	mA
Attenuation Range	0		60	dB

Mechanical Specifications

Size
Length

2 in [50.8 mm]

Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control

PE70A2000



Width	1.8 in [45.72 mm]
Height	0.5 in [12.7 mm]
Weight	0.153 lbs [69.4 g]
Input Connector	SMA Female
Output Connector	SMA Female
Power and Control	15-Pin D-Subminiature

Environmental Specifications

Temperature

Operating Range	-55 to +85 deg C
Storage Range	-65 to +125 deg C
Humidity	MIL-STD-202F, METHOD 103B COND. B
Shock	MIL-STD-202F, METHOD 213B COND. B
Vibration	MIL-STD-202F, METHOD 204D COND. B
Altitude	MIL-STD-202F, METHOD 105C COND. B
Temperature Cycle	MIL-STD-202F, METHOD 107
Salt Spray	MIL-STD-202F, METHOD 105C COND. B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

- Values at +25 °C, sea level

ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.


Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control



PE70A2000

Functional Block Diagram

Performance Data




Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control




PE70A2000

10dB Attenuation



20dB Attenuation




Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control



PE70A2000

40dB Attenuation



60dB Attenuation




Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control




PE70A2000

Delay 0 to 60 dB



Delay 60 to 0 dB



Channel 1 (Yellow): RF output

Channel 2 (Green): TTL Input from Signal Generator

Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control

PE70A2000



Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control PE70A2000](https://www.pasternack.com/60db-voltage-variable-attenuator-pin-diode-4-ghz-sma-pe70a2000-p.aspx)

URL: <https://www.pasternack.com/60db-voltage-variable-attenuator-pin-diode-4-ghz-sma-pe70a2000-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE70A2000 CAD Drawing

Voltage Variable PIN Diode Attenuator, 0 to 60 dB, 2 GHz to 4 GHz, SMA, 15-Pin D-Subminiature Control

