



SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm

Electromechanical Relay Switches Technical Data Sheet

PE71S7293

Features

- Single Pole Six Throw (SP6T) Electromechanical Relay Switch
- DC to 43 GHz Frequency Range
- Normally Open Actuator
- TTL Logic Control
- Indicators
- Suppression Diodes
- 2M Lifecycle Rating
- Insertion Loss 0.6 dB typ
- Isolation > 70 dB typ
- VSWR as low as 1.25:1 max
- 15 Pin D-Sub Connector for all DC Command Control Functions
- +12 Volt DC Bias
- 2.92mm Female Connectors
- -25°C to +65°C Operating Temperature
- Up to 10 Watts Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Description

The PE71S7293 is a Single Pole Six Throw (SP6T) electromechanical relay switch that operates across an ultra wide frequency range from DC to 43 GHz and can handle up to 10 Watts of Average Power in a break before make condition. The 50 Ohm design is rated for 2 million lifecycles and features a Normally Open Actuator where the selected position remains active with constant voltage, all positions are open when voltage is removed. Additional features include TTL logic control, Indicators to monitor the switch position, and Suppression Diodes which limit voltage spikes or reverse current. Impressive typical performance includes 0.6 dB insertion loss and isolation greater than 70 dB. This switch requires +12 Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports 2.92mm female connectors and a 15 Pin D-Sub connector for all DC command control functions. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = 25°C, DC Voltage = 12 Vdc)

Switch Type	SP6T
Actuator Type	Normally Open
Actuator Options	Indicators, TTL Logic, Diodes
TTL Control	on: 2.4 to 5 Volts off: 0 to 0.8 Volts

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		43	GHz
Operating Voltage	11	12	13	Volts
Actuating Set Current			400	mA
VSWR		1.4:1	2.1:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm PE71S7293](#)



SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7293

Insertion Loss		0.6	1.6	dB
Isolation	40	85		dB
Input Power			10	Watts
Switching Time			20	ms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12	12 to 18	18 to 28	28 to 34	GHz
VSWR, Max	1.25:1	1.4:1	1.5:1	1.8:1	1.8:1	
Insertion Loss, Max	0.2	0.4	0.5	0.9	1	dB
Isolation, Min	70	60	60	60	60	dB

Performance by Frequency

Description	F6	F7	F8	F9	F10	Units
Frequency Range	34 to 40	40 to 43				GHz
VSWR, Max	1.8:1	2.1:1				
Insertion Loss, Max	1.3	1.6				dB
Isolation, Min	50	40				dB

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width/Diameter	1.75 in [44.45 mm]
Height	1.75 in [44.45 mm]
Weight	0.28 lbs [127.01 g]
Finish	Electroless Nickel

Connectors

RF Connector Type	2.92mm Female
Control Connector	D-Subminiature

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
Storage Range	-55 to +100 deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm PE71S7293](#)



SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7293

Shock

MIL-STD-202 Method 213, Condition D, 500G (non operational)

Vibration


MIL-STD-202 Method 204, Condition D, 10G RMS (non operational)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm PE71S7293](#)



SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7293



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm PE71S7293](#)





SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7293

Power Handling vs. Frequency



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm PE71S7293](#)



SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm

Electromechanical Relay Switches Technical Data


PE71S7293

SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm PE71S7293](https://www.pasternack.com/sp6t-electromechanical-relay-normally-open-switch-43-ghz-12v-indicators-ttl-diodes-2.92mm-pe71s7293-p.aspx)


URL: <https://www.pasternack.com/sp6t-electromechanical-relay-normally-open-switch-43-ghz-12v-indicators-ttl-diodes-2.92mm-pe71s7293-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.



PE71S7293 CAD Drawing

SP6T, Electromechanical Relay Normally Open Switch, DC to 43 GHz,
12VDC, 10W, Indicators, TTL, Diodes, D-Sub, 2.92mm



TRUTH TABLE/PIN ASSIGNMENT:

TERMINALS	RF PATH						INDICATOR					
	J1	J2	J3	J4	J5	J6	7	8	9	10	11	12
LOGIC INPUT PINS												
1 ("I")	ON	OFF	OFF	OFF	OFF	OFF	ON	OFF	OFF	OFF	OFF	OFF
2 ("I")	OFF	ON	OFF	OFF	OFF	OFF	OFF	ON	OFF	OFF	OFF	OFF
3 ("I")	OFF	OFF	ON	OFF	OFF	OFF	OFF	OFF	ON	OFF	OFF	OFF
4 ("I")	OFF	OFF	OFF	ON	OFF	OFF	OFF	OFF	OFF	ON	OFF	OFF
5 ("I")	OFF	OFF	OFF	OFF	ON	OFF	OFF	OFF	OFF	OFF	ON	OFF
6 ("I")	OFF	OFF	OFF	OFF	OFF	ON	OFF	OFF	OFF	OFF	OFF	ON

PIN 13: IND COM
PIN 14: Vsw +12VDC
PIN 15: GND

RF POSITION
SCHEMATIC

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.2 [.5] FRACTIONS
XX = ±.02 [.5] ± 1/32
XXX = ±.005 [.13] ANGLES ± 1°
CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

SP6T, NO, 43GHz, 12VDC, indicators, TTL, diodes, 2.92mm, D-Sub

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE

SHEET 2 OF 2

REV A

ITEM NO.

PE71S7293

DRAWN BY

BPUCHASKI

CAGE CODE

53919

SIZE

A

REV A