

SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles



PE71S6348

Features

- Single Pole Double Throw
- DC to 12 GHz Frequency Range
- Isolation greater than 90 dB typical
- 2M Cycle Min Operating Life
- +12 Volt DC
- 600 Watt average Power
- Failsafe Actuator
- -25 to +70°C Operating Temperature
- Insertion Loss as low as 0.3 dB Max
- VSWR as low as 1.4:1 max
- N Female RF connectors
- 9 Pin D-Sub Connector for DC Control
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request

Applications

- High Performance Relay Switch
- Military Communications
- Communications Systems
- Test & Measurement

Description

The PE71S6348 is a Single Pole Double Throw (SPDT) electromechanical relay switch that operates across a wide frequency range of DC to 12 GHz and can handle up to 600 Watts of CW input power in a break before make condition. The design features a Failsafe actuator and is rated for 2M life cycles for high reliability operation. Impressive performance includes insertion loss less than 0.3 dB typical and isolation greater than 90 dB typical. The Failsafe actuator has a +12 Vdc bias voltage, and operates over a temperature range of -25°C to +70°C. The rugged and compact package assembly supports N Female connectors and a 9 Pin D-Sub Connector for DC Control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = +25°C, DC Voltage = 12 Vdc)

Switch Type	SPDT
Actuator Type	Failsafe
Switching Sequence	Break before Make

Description	Min	Typ	Max	Units
Frequency Range	DC		12	GHz
Impedance		50		Ohms
Operating Voltage	11	12	13	Volts
Actuating Current @ 12 Volts		200		mA
VSWR		1.25:1	1.4:1	
Insertion Loss		0.3	0.5	dB
Isolation	60	90		dB
Input Power (CW)			200	Watts
Switching Time			20	ms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 4	4 to 8	8 to 12		GHz
VSWR, Max	1.25:1	1.3:1	1.4:1	1.4:1		
Insertion Loss, Max	0.3	0.4	0.4	0.5		dB

SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles



PE71S6348

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Isolation, Min	90	80	70	60		dB
Power In, Typ (CW)	600	300	230	200		Watts

Mechanical Specifications

Size

Weight	0.415 lbs [188.24 g]
Body Material and Plating	Aluminum
Package Type	Connectorized
Operating Life	2,000,000 Cycles

Connectors

RF Connector Type	N Female
RF Connector Contact Material & Plating	Beryllium Copper, Gold
RF Connector Body Material & Plating	Aluminum, Nickel
Control Connector	9-Pin D-Subminiature

Environmental Specifications

Temperature

Operating Range	-25 to +70 deg C
Storage Range	-55 to +100 deg C
Shock	MIL-STD-202 Method 213, Cond. D 500G Non Operating
Vibration	MIL-STD-202 Method 214, Cond. D 10G RMS Non Operating

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data



Notes:

SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles



PE71S6348


Typical Performance Data



SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles




PE71S6348



SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles



PE71S6348



Environmental and Test Conditions:

- Ambient temperature of 25°C or less
- Altitude: Sea Level
- Load VSWR: 1.20:1 max.
- Cold Switching

SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles



PE71S6348

SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles PE71S6348](https://www.pasternack.com/spdt-electromechanical-relay-failsafe-switch-12-ghz-200w-12v-n-pe71s6348-p.aspx)

URL: <https://www.pasternack.com/spdt-electromechanical-relay-failsafe-switch-12-ghz-200w-12v-n-pe71s6348-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE71S6348 CAD Drawing

SPDT Electromechanical Relay Failsafe Switch, DC to 12 GHz, up to 600W, 12V, N, 2M Lifecycles

