



SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm

Electromechanical Relay Switches Technical Data Sheet

PE71S8024

Features

- Single Pole Six Throw (SP6T) Electromechanical Relay Switch
- DC to 53 GHz Frequency Range
- Latching Actuator
- Terminated
- 1M Lifecycle Rating
- Insertion Loss 0.8 dB typ
- Isolation 80 dB typ
- VSWR as low as 1.3:1 max
- Solder Terminal Pins for DC Control
- +28 Volt DC Bias
- 2.4mm Female Connectors
- -25°C to +65°C Operating Temperature
- Up to 3 Watt Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions
- Reset/Set Feature

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Description

The PE71S8024 is a Single Pole Six Throw (SP6T) electromechanical relay switch that operates across an ultra wide frequency range from DC to 52 GHz and can handle up to 3 Watts of Average Power in a break before make condition. The 50 Ohm design is rated for 1 million lifecycles and has a Latching Actuator that magnetically latches in place after the control voltage is removed. For power sensitive applications, this is the best actuator option. The output ports are terminated in 50 ohms when switched in the isolation (off) state. An additional feature includes a Reset/Set functionality. Impressive typical performance includes 0.8 dB insertion loss and isolation greater than 80 dB. This switch requires +28 Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports 2.4mm female connectors and solder terminal pins for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = 25°C, DC Voltage = 28 Vdc)

Switch Type SP6T
 Actuator Type Latching
 Actuator Options Reset

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		52	GHz
Operating Voltage	26	28	30	Volts
Actuating Set Current			110	mA
Actuating Reset Current		660		mA
VSWR		1.5:1	2.8:1	
Insertion Loss		0.8	2.3	dB
Isolation	50	80		dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm PE71S8024](#)



SP6T, Terminated, Electromechanical Relay Latching
Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm

Electromechanical Relay Switches Technical Data

PE71S8024

Input Power	3	Watts
-------------	---	-------

Switching Time	20	ms
----------------	----	----

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12.4	12.4 to 18	18 to 26.5	26.5 to 40	GHz
VSWR, Max	1.3:1	1.4:1	1.5:1	1.7:1	1.9:1	
Insertion Loss, Max	0.2	0.4	0.5	0.7	0.9	dB
Isolation, Min	70	60	60	55	50	dB

Performance by Frequency

Description	F6	F7	F8	F9	F10	Units
Frequency Range	40 to 50	50 to 52				GHz
VSWR, Max	2.2:1	2.8:1				
Insertion Loss, Max	1.3	2.3				dB
Isolation, Min	50	50				dB

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width/Diameter	1.75 in [44.45 mm]
Height	1.75 in [44.45 mm]
Weight	0.28 lbs [127.01 g]
Finish	Electroless Nickel

Connectors

RF Connector Type	2.4mm Female
Control Connector	D-Subminiature

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
Storage Range	-55 to +100 deg C

Shock

MIL-STD-202 Method 213, Condition D, 500G (non operational)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm PE71S8024](#)



SP6T, Terminated, Electromechanical Relay Latching
Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm

Electromechanical Relay Switches Technical Data

PE71S8024

Vibration


MIL-STD-202 Method 204, Condition D, 10G RMS (non operational)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm PE71S8024](#)



SP6T, Terminated, Electromechanical Relay Latching
Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm

Electromechanical Relay Switches Technical Data

PE71S8024



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm PE71S8024](#)





SP6T, Terminated, Electromechanical Relay Latching
Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm

Electromechanical Relay Switches Technical Data

PE71S8024

Power Handling vs. Frequency



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm PE71S8024](#)



SP6T, Terminated, Electromechanical Relay Latching
Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm

Electromechanical Relay Switches Technical Data

PE71S8024

SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm PE71S8024](https://www.pasternack.com/sp6t-electromechanical-relay-latching-switch-52-ghz-28v-reset-2.4mm-pe71s8024-p.aspx)


URL: <https://www.pasternack.com/sp6t-electromechanical-relay-latching-switch-52-ghz-28v-reset-2.4mm-pe71s8024-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S8024 CAD Drawing

SP6T, Terminated, Electromechanical Relay Latching Switch, DC to 52GHz, 28VDC, Reset, D-Sub, 2.4mm






PIN ASSIGNMENT :

TERMINALS	RF PATH					
	J1	J2	J3	J4	J5	J6
1 (SET+)	ON	OFF	OFF	OFF	OFF	OFF
2 (SET+)	OFF	ON	OFF	OFF	OFF	OFF
3 (SET+)	OFF	OFF	ON	OFF	OFF	OFF
4 (SET+)	OFF	OFF	OFF	ON	OFF	OFF
5 (SET+)	OFF	OFF	OFF	OFF	ON	OFF
6 (SET+)	OFF	OFF	OFF	OFF	OFF	ON
14 (RESET+)	ALL OFF					

PIN 15, -COM

- ACTUATION CHARACTERISTICS:
- REQUIRES TWO (2) SEQUENTIAL PULSES (RESET & SET)
 - T1 & T2 = 30mSEC MIN
 - T3 = 10mSEC MIN
 - T4 & T5 = 20mSEC MAX



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [.5] FRACTIONS
.XX = ±.02 [.5] ANGLES ± 1°
XXX = ±.005 [.13]
CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0
ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION
SP6T, TERM. 2.4mm, LATCHING, 52GHz, 28VDC, D-SUB



SCALE NONE
SHEET 2 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.