



SP6T, IP64 Rated Electromechanical Relay Normally Open
 Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

Electromechanical Relay Switches Technical Data Sheet

PE71S6552

Features

- Single Pole Four Throw (SP6T) Electromechanical Relay Switch
- IP64 Level 1 Rated
- DC to 18 GHz Frequency Range
- Normally Open Actuator
- TTL
- Suppression Diodes
- 2M Lifecycle Rating
- Insertion Loss 0.2 dB typ
- Isolation > 80 dB typ
- VSWR as low as 1.25:1 max
- +12 Volt DC Bias
- 15 Pin D-SUB Connector for Command Control functions
- SMA Female Connectors
- -54°C to +85°C Operating Temperature
- Up to 90 Watt Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Description

The PE71S6552 is a Ruggedized SP6T electromechanical relay switch that operates across a broadband frequency range from DC to 18 GHz and can handle up to 90W of average power in a break before make condition. The 50 Ohm design is IP64 compliant with a Level 1 moisture seal and specially designed to operate reliably in harsh usage environments and conditions, such as over extreme temperatures and wet or dusty environments. Intrusion protection offers full protection against dust and other particulates. Moisture protection enables resistance to splashes in all directions. The 50 Ohm design is rated for 2 million lifecycles and features a Normally Open Actuator where the selected position remains active with constant voltage, all positions are open when voltage is removed. Additional features include TTL Control Logic, and suppression diodes which limit voltage spikes or reverse current. Impressive typical performance includes 0.2 dB insertion loss and isolation greater than 80 dB. This switch requires +12 Vdc bias voltage and operates over a temperature range of -54°C to +85°C. The rugged and compact package assembly supports SMA female connectors and 15 Pin D-SUB connector for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = 25°C, DC Voltage = 12 Vdc)

Switch Type	SP6T
Actuator Type	Normally Open
Actuator Options	TTL Logic, Diodes
TTL Control	on: 2.4 to 5.5 Volts off: 0 to 0.8 Volts

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
Operating Voltage	11	12	13	Volts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA PE71S6552](#)



SP6T, IP64 Rated Electromechanical Relay Normally Open
Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6552

Actuating Set Current	400	mA
VSWR	1.1:1	1.5:1
Insertion Loss	0.2	0.5
Isolation	80	90
Switching Time	<20	ms Typ

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12	12 to 18			GHz
VSWR, Max	1.25:1	1.4:1	1.5:1			
Insertion Loss, Max	0.2	0.4	0.5			dB
Isolation, Min	80	80	80			dB

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width/Diameter	1.75 in [44.45 mm]
Height	1.75 in [44.45 mm]
Weight	0.126 lbs [57.15 g]

Connectors

RF Connector Type	SMA Female
Control Connector	D-Subminiature

Environmental Specifications

Temperature

Operating Range	-54 to +85 deg C
Storage Range	-55 to +100 deg C

Ingress Protection (IP) Rating	IP64
Shock	MIL-STD-202 Method 213, Condition D, 500 G (non oper)

Vibration	MIL-STD-202 Method 204, Condition D, 10G RMS (non oper)
-----------	---

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA PE71S6552](#)



SP6T, IP64 Rated Electromechanical Relay Normally Open
Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

Electromechanical Relay Switches Technical Data


PE71S6552

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA PE71S6552](#)



SP6T, IP64 Rated Electromechanical Relay Normally Open
Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6552



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA PE71S6552](#)





SP6T, IP64 Rated Electromechanical Relay Normally Open
Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6552

Power Handling vs. Frequency



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA PE71S6552](#)



SP6T, IP64 Rated Electromechanical Relay Normally Open
Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

Electromechanical Relay Switches Technical Data

PE71S6552

SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA PE71S6552](https://www.pasternack.com/sp6t-electromechanical-relay-normally-open-switch-18-ghz-ttl-diodes-sma-pe71s6552-p.aspx)

URL: <https://www.pasternack.com/sp6t-electromechanical-relay-normally-open-switch-18-ghz-ttl-diodes-sma-pe71s6552-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

SP6T, IP64 Rated Electromechanical Relay Normally Open Switch, DC to 18GHz, 90W, TTL, Diodes, 12VDC, SMA

REVISION				
ZONE	REV.	DESCRIPTION	DATE	
	A	INITIAL RELEASE	02/08/2023	CHANGED BY DMAY
				APPROVED BY TGALLA





NOTES:

1. LABEL PER ILS-100-02. FOR INTERNAL REFERENCE ONLY.
LABEL LOCATION FOR REFERENCE ONLY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		 		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES:		SCALE			
X ± .2 [5] FRACTIONS		SHEET			
XX ± .02 [.5] ± 1/32		NONE			
XXX ± .005 [.13] ANGLES ± 1°		1 OF 2			
CABLE LENGTH TOLERANCES:		DESCRIPTION			
±12 [305] ≤ +1 [25] / -0		Website: www.Pasternack.com			
>12 [305] ≤ 60 [1524] = +2 [51] / -0		Phone: 1.866.727.8376 1.949.261.1920			
>60 [1524] ≤ 120 [3048] = +4 [102] / -0		SP6T, SMA, NO, 18GHz, 12VDC, TTL, DIODES, D-SUB,			
>120 [3048] ≤ 300 [7620] = +6 [152] / -0		RUGGEDIZED			
>300 [7620] = +5% / -0		SIZE		CAGE CODE	DRAWN BY
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE		A		53919	DMAY
		ITEM NO.		PE71S6552	
		REV		A	





TRUTH TABLE/PIN ASSIGNMENT :
PIN ASSIGNMENT

TERMINALS LOGIC INPUT PIN ASSIGNMENT	RF PATH					
	J1	J2	J3	J4	J5	J6
1("1")	ON	OFF	OFF	OFF	OFF	OFF
2("1")	OFF	ON	OFF	OFF	OFF	OFF
3("1")	OFF	OFF	ON	OFF	OFF	OFF
4("1")	OFF	OFF	OFF	ON	OFF	OFF
5("1")	OFF	OFF	OFF	OFF	ON	OFF
6("1")	OFF	OFF	OFF	OFF	OFF	ON

PIN 9, -COM

PIN 8, Vsw +12VDC

RF POSITION
SCHEMATIC

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [.5] FRACTIONS
.XX = ±.02 [.5] ±.132
.XXX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE

PE PASTERNAK
an INFINITI® brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

SP6T, SMA, NO, 18GHz, 12VDC, TTL, DIODES, D-SUB,
RUGGEDIZED

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

SIZE A CASE CODE A 53919 DRAWN BY DMAY ITEM NO. PE71S6552 REV A

SCALE NONE SHEET 2 OF 2

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5