



SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data Sheet

PE71S7288

Features

- Single Pole Four Throw (SP4T) Electromechanical Relay Switch
- DC to 43 GHz Frequency Range
- Normally Open Actuator
- 2M Lifecycle Rating
- Insertion Loss 0.6 dB typ
- Isolation > 70 dB typ
- VSWR as low as 1.25:1 max
- Solder Terminal Pins for DC Control
- +12 Volt DC Bias
- 2.92mm Female Connectors
- -25°C to +65°C Operating Temperature
- Up to 10 Watts Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Description

The PE71S7288 is a Single Pole Four Throw (SP4T) electromechanical relay switch that operates across an ultra wide frequency range from DC to 43 GHz and can handle up to 10 Watts of Average Power in a break before make condition. The 50 Ohm design is rated for 2 million lifecycles and features a Normally Open Actuator where the selected position remains active with constant voltage, all positions are open when voltage is removed. Impressive typical performance includes 0.6 dB insertion loss and isolation greater than 70 dB. This switch requires +12 Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports 2.92mm female connectors and solder terminal pins for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = 25°C, DC Voltage = 12 Vdc)

Switch Type
Actuator Type

SP4T
Normally Open

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		43	GHz
Operating Voltage	11	12	13	Volts
Actuating Set Current			400	mA
VSWR		1.4:1	2.1:1	
Insertion Loss		0.6	1.6	dB
Isolation	40	85		dB
Input Power			10	Watts
Switching Time			20	ms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm PE71S7288](#)



SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7288

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12	12 to 18	18 to 28	28 to 34	GHz
VSWR, Max	1.25:1	1.4:1	1.5:1	1.8:1	1.8:1	
Insertion Loss, Max	0.2	0.4	0.5	0.9	1	dB
Isolation, Min	70	60	60	60	60	dB

Performance by Frequency

Description	F6	F7	F8	F9	F10	Units
Frequency Range	34 to 40	40 to 43				GHz
VSWR, Max	1.8:1	2.1:1				
Insertion Loss, Max	1.3	1.6				dB
Isolation, Min	50	40				dB

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width/Diameter	1.75 in [44.45 mm]
Height	1.75 in [44.45 mm]
Weight	0.22 lbs [99.79 g]
Finish	Electroless Nickel

Connectors

RF Connector Type	2.92mm Female
Control Connector	Solder Terminals

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
Storage Range	-55 to +100 deg C

Shock

MIL-STD-202 Method 213, Condition D, 500G (non operational)

Vibration

MIL-STD-202 Method 204, Condition D, 10G RMS (non operational)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm PE71S7288](#)



SP4T, Electromechanical Relay Normally Open Switch, DC
to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data


PE71S7288

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm PE71S7288](#)



SP4T, Electromechanical Relay Normally Open Switch, DC
to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7288



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm PE71S7288](#)





SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7288

Power Handling vs. Frequency



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm PE71S7288](#)



SP4T, Electromechanical Relay Normally Open Switch, DC
to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7288

SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm PE71S7288](https://www.pasternack.com/sp4t-electromechanical-relay-normally-open-switch-43-ghz-12v-2.92mm-pe71s7288-p.aspx)

URL: <https://www.pasternack.com/sp4t-electromechanical-relay-normally-open-switch-43-ghz-12v-2.92mm-pe71s7288-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

© 2020 Pasternack Enterprises All Rights Reserved




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

1. LABEL PER ILS-100-02 FOR INTERNAL REFERENCE ONLY
LABEL LOCATION FOR REFERENCE ONLY

THE
PAR
THE
EXP

PE71S7288 CAD Drawing

SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm



TRUTH TABLE/PIN ASSIGNMENT:
PIN ASSIGNMENT

TERMINALS	PIN ASSIGNMENT	RF PATH
		J1 J2 J3 J4
1		ON OFF OFF OFF
2		OFF ON OFF OFF
3		OFF OFF ON OFF
4		OFF OFF OFF ON

PIN -C.-COM

RF POSITION
SCHEMATIC



INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE

SHEET 2 OF 2

Website: www.Pasternack.com

Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

SP4T , NO, 43GHz, 12VDC, 2.92mm, solder terminal

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.2 [.5] FRACTIONS
XX = ±.02 [.5]
XXX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤12 [305] = +1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.