

Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data Sheet

PE71S7295

Features

- Transfer Electromechanical Relay Switch
- DC to 43 GHz Frequency Range
- Failsafe Actuator
- 2M Lifecycle Rating
- Insertion Loss 0.6 dB typ
- Isolation > 80 dB typ
- VSWR as low as 1.2:1 max
- Solder Terminal Pins for DC Control
- +28 Volt DC Bias
- 2.92mm Female Connectors
- -25°C to +65°C Operating Temperature
- Up to 10 Watt Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Description

The PE71S7295 is a Transfer electromechanical relay switch that operates across an ultra wide frequency range from DC to 43 GHz and can handle up to 10 Watts of Average Power in a break before make condition. The 50 Ohm design is rated for 2 million lifecycles and features a Failsafe Actuator. Impressive typical performance includes 0.6 dB insertion loss and isolation greater than 80 dB. This switch requires +28 Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports 2.92mm female connectors and solder terminal pins for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = 25°C, DC Voltage = 28 Vdc)

Switch Type
Actuator Type

Transfer
Failsafe

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		43	GHz
Operating Voltage	26	28	30	Volts
Actuating Set Current			160	mA
VSWR		1.4:1	2:1	
Insertion Loss		0.6	1.3	dB
Isolation	50	85		dB
Input Power			10	Watts
Switching Time			20	ms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm PE71S7295](#)



Transfer, Electromechanical Relay Failsafe Switch, DC
to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7295

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12.4	12.4 to 26.5	26.5 to 40	40 to 43	GHz
VSWR, Max	1.2:1	1.3:1	1.4:1	1.8:1	2:1	
Insertion Loss, Max	0.2	0.4	0.7	1	1.3	dB
Isolation, Min	80	75	65	50	50	dB

Mechanical Specifications

Size

Length	2 in [50.8 mm]
Width/Diameter	2.16 in [54.86 mm]
Height	1.26 in [32 mm]
Weight	0.26 lbs [117.93 g]
Finish	Electroless Nickel

Connectors

RF Connector Type	2.92mm Female
Control Connector	Solder Terminals

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
Storage Range	-55 to +100 deg C

Shock	MIL-STD-202 Method 213, Condition D, 500G (non operational)
Vibration	MIL-STD-202 Method 204, Condition D, 10G RMS (non operational)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm PE71S7295](#)




Transfer, Electromechanical Relay Failsafe Switch, DC
to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7295

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm PE71S7295](#)




Transfer, Electromechanical Relay Failsafe Switch, DC
to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7295



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm PE71S7295](#)





Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7295

Power Handling vs. Frequency



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm PE71S7295](#)



Transfer, Electromechanical Relay Failsafe Switch, DC
to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm

Electromechanical Relay Switches Technical Data

PE71S7295

Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm PE71S7295](https://www.pasternack.com/transfer-electromechanical-relay-failsafe-switch-43-ghz-28v-2.92mm-pe71s7295-p.aspx)

URL: <https://www.pasternack.com/transfer-electromechanical-relay-failsafe-switch-43-ghz-28v-2.92mm-pe71s7295-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.


PE71S7295 CAD Drawing

Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm



PE71S7295 CAD Drawing

Transfer, Electromechanical Relay Failsafe Switch, DC to 43 GHz, 28VDC, 10W, Solder Terminals, 2.92mm



VOLTAGE	RF PATH
DE-ENERGIZED	J1-J2, J3-J4
ENERGIZED	J1-J3, J2-J4

SCHEMATIC

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.2	[.5]	FRACTIONS
XX = ±.02	[.13]	± 1/32
XXX = ±.005	[.13]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤12 [305]	±.1 [25]	-0
>12 [305]	≤.60 [1524]	±.2 [51] / -0
>60 [1524]	≤1.20 [3048]	±.4 [102] / -0
>120 [3048]	≤3.00 [7620]	±.6 [152] / -0
>300 [7620]	±.5% / -0	

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE

PE PASTERNAK
an INFINITI[®] brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

TRAN, 2.92mm, failsafe, 43GHz, 28VDC, solder terminal

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	BPUCHASKI	PE71S7295	A

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE

NONE

SHEET

2 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.