

## 0 to 20 dB Variable Attenuator, SMA Female to SMA Female Rated to 5 Watts from 8 GHz to 18 GHz



### PE7502-20

#### Features

- 20 dB Attenuation Level
- Rotary Dial Design for Continuous Adjustment
- Frequency Range 8 GHz to 18 GHz Range
- SMA Female Connectorized Design
- Max VSWR 1.6:1
- Max Power Rating: 5W (CW)

#### Applications

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems

#### Description

Pasternack PE7502-20 is a continuously variable attenuator that has 20 dB of total attenuation with rotary dial design for continuous attenuation level adjustment with +/- 2.0 dB flatness across a frequency range of 8 GHz to 18 GHz. With SMA female gender for connector 1 and a SMA female for connector 2. This microwave variable attenuator design is tried and true technology that offers exceptional RF performance characteristics that include 0.5 dB maximum insertion loss and a maximum VSWR of 1.6:1. Our continuously variable attenuator is rated to 5 Watts (CW).

#### Configuration

Design	Continuously Variable Attenuator
Body Material and Plating	Aluminum

#### Electrical Specifications Values at 25°C, sea level

Description	Minimum	Typical	Maximum	Units
Frequency Range	8		18	GHz
Impedance		50		Ohms
Attenuation Value		0 to 20		dB
Step Type		Dial		
Input Power (CW)			5	Watts
Peak Power			3	kWatts
Insertion Loss			0.5	dB
VSWR			1.6:1	

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	8 to 18					GHz
Attenuation Accuracy	2					dB

#### Mechanical Specifications

##### Temperature

##### Size

Length  
Width

2 in [50.8 mm]  
1.25 in [31.75 mm]

0 to 20 dB Variable Attenuator, SMA Female to SMA Female Rated to 5 Watts from 8 GHz to 18 GHz



## PE7502-20

Height	0.5 in [12.7 mm]
Weight	0.02 lbs [9.07 g]

### Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SMA Female

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25 °C, sea level

0 to 20 dB Variable Attenuator, SMA Female to SMA Female Rated to 5 Watts from 8 GHz to 18 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0 to 20 dB Variable Attenuator, SMA Female to SMA Female Rated to 5 Watts from 8 GHz to 18 GHz PE7502-20](#)

URL: <https://www.pasternack.com/20db-continuously-variable-sma-female-sma-female-5-watts-attenuator-pe7502-20-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE7502-20 CAD Drawing

0 to 20 dB Variable Attenuator, SMA Female to SMA Female Rated to 5 Watts from 8 GHz to 18 GHz

