

10 dB Fixed Attenuator, 2.2-5 Male to 2.2-5 Female
Brass Body Rated to 5 Watts, DC to 6 GHz



RF Fixed Attenuators Technical Data Sheet

PE7492-10

Features

- DC to 6 GHz Frequency Range
- 2.2-5 Connectorized Design
- Attenuation 10 dB \pm 1 dB

- Max Power 5 Watts (CW)
- Max VSWR of 1.25:1

Applications

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems
- 5G Cellular bands

Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal. Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 10 dB Fixed Attenuator PE7492-10 is rated to 5 Watts and operates from DC to 6 GHz.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance	50			Ohms
Nominal Attenuation	10			dB
Attenuation Accuracy			\pm 1	dB
VSWR			1.25:1	
Input Power, CW			5	Watts
Input Power, Peak			50	Watts
	8% Duty Cycle, 20us PW			

Mechanical Specifications

Size

Length	2.36 in [59.94 mm]
Width/Diameter	0.79 in [20.07 mm]
Height	0.79 in [20.07 mm]
Weight	0.07 lbs [31.75 g]
Body Material and Plating	Brass, Copper-Tin-Zinc Alloy

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 dB Fixed Attenuator, 2.2-5 Male to 2.2-5 Female Brass Body Rated to 5 Watts, DC to 6 GHz PE7492-10](#)

10 dB Fixed Attenuator, 2.2-5 Male to 2.2-5 Female
Brass Body Rated to 5 Watts, DC to 6 GHz



RF Fixed Attenuators Technical Data Sheet

PE7492-10

Configuration

Design: Fixed, Bidirectional
Design Type: Standard
Package Style: Connectorized

Connectors

Description	Connector 1	Connector 2
Type	2.2-5 Male	2.2-5 Female
Contact Material and Plating	Beryllium Copper, Silver	Beryllium Copper, Silver
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

Environmental Specifications

Temperature

Operating Range: -40 to +75 deg C
Storage Range: -50 to +85 deg C

Humidity

<95%

Shock

IEC 60068-2-27

Vibration

IEC 60068-2-6-Fc

Altitude

<5000m

Thermal Shock

IEC 60068 -2-14-Na

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

10 dB Fixed Attenuator, 2.2-5 Male to 2.2-5 Female Brass Body Rated to 5 Watts, DC to 6 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 dB Fixed Attenuator, 2.2-5 Male to 2.2-5 Female Brass Body Rated to 5 Watts, DC to 6 GHz PE7492-10](#)

URL: <https://www.pasternack.com/10db-fixed-5-watts-attenuator-pe7492-10-p.aspx>

PE7492-10 CAD Drawing

10 dB Fixed Attenuator, 2.2-5 Male to 2.2-5 Female
Brass Body Rated to 5 Watts, DC to 6 GHz

