



2dB RF fixed attenuator 2W, DC to 6GHz,
SMA male to female, Stainless Steel

RF Fixed Attenuators Technical Data Sheet

PE7602-2

Features

- Bidirectional
- DC to 6 GHz Range
- Attenuation 2 +/- 0.5 dB
- 2 Watts Average Input Power
- VSWR <1.15:1

Applications

- Precision Measurements
- Production Systems
- Instrumentation
- Prototyping and Characterization

Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 2 dB Fixed Attenuators PE7602-2 is rated to 2 Watts and operates from DC to 6 GHz. The versatile coaxial package uses SMA male to SMA female connectors and is also REACH and RoHS compliant.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
Nominal Attenuation		2		dB
VSWR			1.15:1	
Input Power, CW			2	Watts
Input Power, Peak			500	Watts
	5μs pulse w/ 0.4% duty cycle			

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2dB RF fixed attenuator 2W, DC to 6GHz, SMA male to female, Stainless Steel PE7602-2](#)



2dB RF fixed attenuator 2W, DC to 6GHz,
SMA male to female, Stainless Steel

RF Fixed Attenuators Technical Data Sheet

PE7602-2

Mechanical Specifications

Size

Length 0.858266 in [21.8 mm]
Width/Diameter 0.31496 in [8 mm]
Height 0.31496 in [8 mm]

Weight

Body Material and Plating 0.01 lbs [4.54 g]
Stainless Steel

Configuration

Design Fixed, Bidirectional

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Female
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Body Material and Plating	Stainless Steel	Stainless Steel

Environmental Specifications

Temperature

Operating Range +125 to -55 deg C

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:

2dB RF fixed attenuator 2W, DC to 6GHz, SMA male to female, Stainless Steel from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2dB RF fixed attenuator 2W, DC to 6GHz, SMA male to female, Stainless Steel PE7602-2](#)

URL:

PE7602-2 CAD Drawing

2dB RF fixed attenuator 2W, DC to 6GHz, SMA male to female, Stainless Steel

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	11/22/2023	DMAY	SPONG



 PASTERNACK® an INFINIT® brand			
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES: $x = \pm 0.02 [0.5]$ $xx = \pm 0.05 [0.13]$ $xxx = \pm 0.025 [0.03]$	FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$	SCALE NONE	SHEET 1 OF 1
CABLE LENGTH TOLERANCES: $\pm 12 [305] \leq 60 [1524] = \pm 12 [305] / -0$ $\pm 12 [305] \leq 120 [3048] = \pm 12 [305] / -0$ $\pm 60 [1524] \leq 300 [7620] = \pm 6 [152] / -0$ $\pm 120 [3048] \leq 300 [7620] = \pm 5% / -0$		DESCRIPTION 2dB RF FIXED ATTENUATOR 2W, DC TO 6GHz, SMA MALE TO FEMALE, STAINLESS STEEL	ITEM NO. PET602-2
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UNDIMENTIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	SIZE A	CAGE CODE 53919	DRAWN BY DMAY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE, WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITES, TECHNOLOGY OR SOFTWARE, WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.