



0.5 GHz to 8 GHz Power Detector, Positive
Output Slope, +23 dBm Max Pin, SMA

Detectors Technical Data Sheet

PE80P1006

Features

- Power Detector with Positive Output Slope
- 500 MHz to 8 GHz
- High Voltage Sensitivity 0.5 mV/uW typ
- Tangential Signal Sensitivity (TSS) -30 dBm typ
- VSWR 1.1:1 typ
- Maximum RF Input Power Handling +23 dBm
- No DC Bias Required
- 50 Ohm Design
- Field Replaceable SMA Connectors, Male input and Female output
- Operational Temperature Range -40°C to +85°C
- Rugged and Compact Aluminum Gold Plated Package Design
- Guaranteed Environmental Test Conditions Altitude, Vibration, Humidity, Shock

Applications

- Test & Measurement
- Military and Commercial Communications
- Military Electronic Systems
- Research & Development


Description

The PE80P1006 is a coaxial packaged Power Detector that operates across a broadband frequency from 500 MHz to 8 GHz. The 50 Ohm design provides a positive output voltage that's proportional to the RF input signal level. Impressive performance includes high voltage sensitivity of 0.5 mV/uW typ, tangential signal sensitivity (TSS) of -30 dBm typ, and low VSWR of 1.1:1 typ. The unit does not require a DC bias voltage, and has maximum RF input power handling of +23 dBm. The low profile pin package is aluminum with Gold plating and supports field replaceable SMA connectors, with a Male RF connector on the input port and a Female RF connector on the output port. With the connectors removed, the package can be drop mounted onto a PWB. The module has an operational temperature range from -40°C to +85°C and is guaranteed to meet a series of environmental test conditions for Altitude, Vibration, Humidity, and Shock.

Electrical Specifications (@ +25°C)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.5		8	GHz
VSWR		1.1:1	1.2:1	
Voltage Sensitivity		0.5		mV/uW
Input Power			23	dBm
Tangential Signal Sensitivity (TSS)		-30		dBm
Operating Temperature Range	-40		85	deg C
Output Polarity		Positive		

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA PE80P1006](#)



0.5 GHz to 8 GHz Power Detector, Positive
Output Slope, +23 dBm Max Pin, SMA

Detectors Technical Data Sheet

PE80P1006

Mechanical Specifications

Size

Length

0.63 in [16 mm]

Width

0.37 in [9.4 mm]

Height

0.41 in [10.41 mm]

Weight

0.01 lbs [4.54 g]

Connector 1

Field Replaceable SMA Male

Connector 2

Field Replaceable SMA Female

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Storage Range

-50 to +105 deg C

Humidity

100% RH at 35 degrees C, 95% RH at 40 degrees C

Shock

20G for 11ms Half Sine Wave, 3 Axis Both Directions


Vibration

25g RMS (15 degrees 2KHz) Endurance, 1 Hour Per Axis

Altitude

30,000 ft (Epoxy Sealed Controlled Environment)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA PE80P1006](#)



0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA

Detectors Technical Data Sheet


PE80P1006

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:


Output DC Voltage VS. Input Power




VSWR @+25°C




VSWR @-45°C



VSWR @+85°C



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA PE80P1006](#)




0.5 GHz to 8 GHz Power Detector, Positive
Output Slope, +23 dBm Max Pin, SMA


Detectors Technical Data Sheet

PE80P1006

Rise time



Fall time



0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA PE80P1006](https://www.pasternack.com/power-detector-sma-positive-500-mhz-8-ghz-pe80p1006-p.aspx)

URL: <https://www.pasternack.com/power-detector-sma-positive-500-mhz-8-ghz-pe80p1006-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE80P1006 CAD Drawing

0.5 GHz to 8 GHz Power Detector, Positive Output Slope, +23 dBm Max Pin, SMA



1 2 3 4 5 6

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/10/2023	KGLEBOVA	TGALLA

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
.XX = ±.02 [.5] ± 1/32
.XXX = ±.005 [.13] ANGLES ± 1°
CABLE LENGTH TOLERANCES:
≤ 12 [305] = ± 1 [25] / - 0
> 12 [305] ≤ 60 [1524] = +2 [51] / - 0
> 60 [1524] ≤ 120 [3048] = +4 [102] / - 0
> 120 [3048] ≤ 300 [7620] = +6 [152] / - 0
> 300 [7620] = +5% / - 0

PE PASTERNAK
an INFINIT® brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

POWER DETECTOR, SMA MALE INPUT, POSITIVE OUTPUT
SLOPE, +23 DBM MAX PIN, 0.5 MHZ TO 8 GHZ

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE NONE SHEET 1 OF 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN
PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE
EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	KGLEBOVA	PE80P1006	A

T-Rev.D2