

WR-102 Waveguide Standard Gain Horn Antenna
Operating from 7 GHz to 11 GHz with a Nominal
10 dBi Gain with UG-1493/U Flange



Waveguide Antennas Technical Data Sheet

PE9857B-10

Features

- WR-102 Rectangular Waveguide Interface
- 7 GHz to 11 GHz

- 10 dBi Nominal Gain
- UG-1493/U Flange

Applications

- Antenna Measurements
- Wireless Communication

- Laboratory Use
- Microwave Radio Systems

Description

The PE9857B-10 WR-102 Proline series standard gain horn antenna (also known as waveguide horn) from Pasternack has a nominal gain of 10 dBi. This WR-102 standard gain horn has a square type flange. The Pasternack 10 dBi WR-102 horn antenna operates from 7 GHz to 11 GHz. The WR-102 PE9857B-10 waveguide horn is US made and TAA compliant. It is part of over 40,000 RF, microwave and millimeter wave components available from Pasternack.

Waveguide standard gain horn antennas are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. Pasternack's WR-102 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. Our WR-102 standard gain horn Proline antennas can ship worldwide the same day as it is purchased as with our other available RF parts.

Configuration

Design
Pattern
Polarization

WR-102 Standard Gain Horn
Directional
Linear

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	7		11	GHz
Impedance		50		Ohms
Nominal Gain		10		dB
VSWR		1.5:1		

Mechanical Specifications

Size
Length
Width
Height

2.39 in [60.71 mm]
1.72 in [43.69 mm]
1.34 in [34.04 mm]

Waveguide Interface

Waveguide Size
Flange Type

WR-102
Square Cover

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-102 Waveguide Standard Gain Horn Antenna Operating from 7 GHz to 11 GHz with a Nominal 10 dBi Gain with UG-1493/U Flange PE9857B-10](#)

WR-102 Waveguide Standard Gain Horn Antenna
Operating from 7 GHz to 11 GHz with a Nominal
10 dBi Gain with UG-1493/U Flange



Waveguide Antennas Technical Data Sheet

PE9857B-10

Flange Designation
Body Material and Plating

UG-1493/U
Aluminum

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

WR-102 Waveguide Standard Gain Horn Antenna Operating from 7 GHz to 11 GHz with a Nominal 10 dBi Gain with UG-1493/U Flange from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-102 Waveguide Standard Gain Horn Antenna Operating from 7 GHz to 11 GHz with a Nominal 10 dBi Gain with UG-1493/U Flange PE9857B-10](#)

URL: <https://www.pasternack.com/wr-102-waveguide-gain-horn-antenna-10db-square-flange-pe9857b-10-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE9857B-10 CAD Drawing

WR-102 Waveguide Standard Gain Horn Antenna Operating from 7 GHz to 11 GHz with a Nominal 10 dBi Gain with UG-1493/U Flange

