

WR-284 Waveguide Standard Gain Horn Antenna
Operating From 2.6 GHz to 3.95 GHz With a
Nominal 10 dBi Gain With CMR-284 Flange



Waveguide Antennas Technical Data Sheet

PE9863B-10

Features

- WR-284 Rectangular Waveguide Interface
- 2.6 GHz to 3.95 GHz

- 10 dBi Nominal Gain
- CMR-284 Cover Flange

Applications

- Antenna Measurements
- Wireless Communication

- Laboratory Use
- Microwave Radio Systems

Description

The PE9863B-10 WR-284 Proline series standard gain horn antenna (also known as waveguide horn) from Pasternack has a nominal gain of 10 dBi. This WR-284 standard gain horn has a CMR-284 type flange. The Pasternack 10 dBi WR-284 horn antenna operates from 2.6 GHz to 3.95 GHz. The WR-284 PE9863B-10 waveguide horn is US made and TAA compliant. It is part of over 40,000 RF, microwave and millimeter wave components available from Pasternack.

Waveguide standard gain horn antennas are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. Pasternack's WR-284 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. Our WR-284 standard gain horn Proline antennas can ship worldwide the same day as it is purchased as with our other available RF parts.

Configuration

Design
Pattern
Polarization

WR-284 Standard Gain Horn
Directional
Linear

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2.6		3.95	GHz
Impedance		50		Ohms
Nominal Gain		10		dB
VSWR		1.5:1		

Mechanical Specifications

Size
Length
Width
Height

7.5 in [190.5 mm]
4.91 in [124.71 mm]
3.65 in [92.71 mm]

Waveguide Interface

Waveguide Size
Flange Type

WR-284
CMR-284

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-284 Waveguide Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz With a Nominal 10 dBi Gain With CMR-284 Flange PE9863B-10](#)

WR-284 Waveguide Standard Gain Horn Antenna
Operating From 2.6 GHz to 3.95 GHz With a
Nominal 10 dBi Gain With CMR-284 Flange



Waveguide Antennas Technical Data Sheet

PE9863B-10

Body Material and Plating

Aluminum

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

WR-284 Waveguide Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz With a Nominal 10 dBi Gain With CMR-284 Flange from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-284 Waveguide Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz With a Nominal 10 dBi Gain With CMR-284 Flange PE9863B-10](#)

URL: <https://www.pasternack.com/wr-284-waveguide-gain-horn-antenna-10db-square-flange-pe9863b-10-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE9863B-10 CAD Drawing

WR-284 Waveguide Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz With a Nominal 10 dBi Gain With CMR-284 Flange

