

SMB Plug to BNC Male Adapter

PE9135



Configuration

- SMB Plug Connector 1
- BNC Male Connector 2

Features

- SMB interface compliant with MIL-STD-348A
- BNC interface compliant with MIL-STD-348A
- 50 Ohms Impedance
- Straight Body Geometry
- 30 μ -in minimum contact plating
- Gold Plated Beryllium Copper Contact

Applications

- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE9135 SMB plug to BNC male adapter is part of our full line of RF components available for same-day shipping. Our SMB to BNC adapter has a plug to male gender configuration. PE9135 SMB plug to BNC male adapter operates to 4 GHz.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
Impedance		50		Ohms
Operating Voltage (AC)			335	Vrms

Electrical Specification Notes:

Values at 25°C, sea level.

Mechanical Specifications

Size

Length	1.20 in [30.48 mm]
Width	0.57 in [14.48 mm]
Height	0.57 in [14.48 mm]
Weight	0.03 lbs [14.97 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard
Interface Specification	MIL-STD-348A	MIL-STD-348A

SMB Plug to BNC Male Adapter

PE9135



Material Specifications

		Connector 1		Connector 2	
Description	Material	Plating	Material	Plating	
Type	SMB Plug		BNC Male		
Contact	Beryllium Copper	Gold 30 μ -in minimum	Beryllium Copper	Gold 30 μ -in minimum	
Insulation	PTFE		PTFE		
Body	Brass	Nickel 100 μ -in minimum	Brass	Nickel 100 μ -in minimum	
Gasket	Silicone		Silicone		
Coupling Nut	Brass	Nickel 100 μ -in minimum	Brass	Nickel 100 μ -in minimum	

Environmental Specifications

Temperature

Operating Range -65 to +165 °C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

SMB Plug to BNC Male Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMB Plug to BNC Male Adapter PE9135](#)


URL: <https://www.pasternack.com/smb-plug-bnc-male-straight-adapter-pe9135.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE9135 CAD Drawing

SMB Plug to BNC Male Adapter

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	UPDATED PER ECO-14283	02/10/2025	HBAKKE	SRAUTUS



		  INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
		SCALE	1 OF 1
		SHEET	
PASTERNACK® an INFINITE® brand		Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920	
PASTERNACK an INFINITE® brand		SMB PLUG TO BNC MALE ADAPTER	
		ITEM NO. PE9135	
		REV B	
DESCRIPTION	SMB PLUG TO BNC MALE ADAPTER		
	SIZE	CAGE CODE	DRAWN BY
A	53919	H BAKKE	2
<small>PRINTED ON 04/01/2014</small>			

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE, WHETHER WRITTEN OR ORAL, IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.