

RF Adapter, 45 Degree Angle TNC jack
to TNC jack 18GHz VSWR1.2



RF Adapters Technical Data Sheet

PE91601

Configuration

- TNC Female Connector 1
- TNC Female Connector 2
- 50 Ohm
- 45 Degree Body Geometry

Features

- Max VSWR of 1.2:1 up to 18 GHz
- Gold over Nickel Plated Beryllium Copper Contact

Applications

- General Purpose Test

Description

TNC adapter PE91601 from Pasternack Enterprises is part of a very large selection of in-stock interconnect RF components. Our TNC to TNC adapter is a coaxial adapter design with a 50 Ohm impedance. This 50 Ohm TNC adapter is manufactured to precise RF adapter specifications and has a maximum VSWR of 1.200.

Our in-series connection type RF adapter, which operates to 18 GHz makes connections in tight spaces easier. This passivated stainless steel RF adapter can be used to make connections between two connector types that would not otherwise mate. This TNC adapter contains beryllium copper contacts with gold over nickel contact plating.

This TNC to TNC adapter is constructed with female gender on side 1 and female on side 2. PE91601 TNC female to TNC female coaxial adapter from Pasternack has a 45-degree angled body ideal for routing RF/Microwave signals in tight spaces. Additionally, RF adapters can be utilized to protect connectors on expensive equipment where the number of connect and disconnect cycles is high.

Pasternack TNC female to TNC female adapter is part of over one million RF microwave and millimeter wave components in stock. 45-degree angle RF TNC adapter is ready for same day purchase and shipping worldwide. We also stock and/or custom build TNC coaxial cables that ship quickly from our facility for all your RF adapter component needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.2:1	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 4	4 to 8	8 to 12	12 to 18	GHz
Insertion Loss, Max	0.07	0.14	0.198	0.242	0.297	dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RF Adapter, 45 Degree Angle TNC jack to TNC jack 18GHz VSWR1.2 PE91601](#)



RF Adapter, 45 Degree Angle TNC jack
to TNC jack 18GHz VSWR1.2

RF Adapters Technical Data Sheet

PE91601

Mechanical Specifications

Size

Length	1.48 in [37.59 mm]
Width	0.51 in [12.95 mm]
Height	0.90 in [22.89 mm]
Weight	0.04 lbs [18.14 g]

Description	Connector 1	Connector 2
Type	TNC Female	TNC Female
Polarity	Standard	Standard

Material Specifications

Description	Connector 1			Connector 2	
	Material	Plating	Material	Plating	
Type	TNC Female		TNC Female		
Contact	Beryllium Copper	Gold over Nickel	Beryllium Copper	Gold over Nickel	
Outer Conductor Passivated Stainless Steel			Passivated Stainless Steel		
Body	Passivated Stainless Steel		Passivated Stainless Steel		

Environmental Specifications

Temperature

Operating Range

-65 to +165 °C

Humidity

Thermal Shock

Salt Spray

MIL-STD-202, Method 206

MIL-STD-202, Method 107, Condition B

MIL-STD-202, Method 101, Condition B

Compliance Certifications

(see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RF Adapter, 45 Degree Angle TNC jack to TNC jack 18GHz VSWR1.2 PE91601](#)

RF Adapter, 45 Degree Angle TNC jack
to TNC jack 18GHz VSWR1.2



RF Adapters Technical Data Sheet

PE91601

RF Adapter, 45 Degree Angle TNC jack to TNC jack 18GHz VSWR1.2 from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RF Adapter, 45 Degree Angle TNC jack to TNC jack 18GHz VSWR1.2 PE91601](#)


URL: <https://www.pasternack.com/tnc-female-to-tnc-female-45-degree-adapter-pe91601-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE91601 CAD Drawing

RF Adapter, 45 Degree Angle TNC jack to TNC jack 18GHz VSWR1.2

REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
A	INITIAL RELEASE	11/03/2022	DWANG	



 PASTERNACK an INFINITE brand	
THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNACK CORPORATION. ALL RIGHTS RESERVED.	
SHEET	1 OF 1
SCALE	N/A
ITEM NO.	PE91601
SIZE	A
CAGE CODE	53919
DRAWN BY	AKRESOWSKI
REV	A

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS
TOLERANCES:

X = ± 2 [5.08] FRACTIONS
.XX = ± .02 [.51] ± 1/32
.XXX = ± .005 [.13] ANGLES ± 1°
CABLE LENGTH (L) TOLERANCES:
L ≤ 12 [305] ± +1 [25] / -0
12 [305] < L ≤ 60 [1524] ± +2 [51] / -0
60 [1524] < L ≤ 120 [3048] ± +4 [102] / -0
120 [3048] < L ≤ 300 [7620] ± +6 [152] / -0
300 [7620] < L = +5%L / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.