



3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female

Antennas Technical Data Sheet

PEANLP1010

Features

- Frequency coverage for 3400 MHz to 3600 MHz
- Very High Gain 14 dBi Directional Antenna
- Each connector covers wide band of frequencies
- Easy Install universal mounting bracket provided
- Weatherproof ABS radome
- Pigtail – 9 inches
- N-Type Female connector

Applications

- Point-to-point, LTE-M, NB-IoT, IoT, M2M applications
- 5G / 4G LTE B22 / CBRS operation supported
- 5G Bands supported - n48, n77, n78
- DAS (Distributed Antenna Systems)
- Public safety, utilities, CCTV and local radio coverage
- Smart cities expansion for coverage and IOT / IIOT

Description

Pasternack's PEANLP1010 high gain log periodic antenna is designed to operate from 3400 to 3600 MHz. With 14 dBi of gain, PEANLP1010 is ideal for boosting 5G, LTE, CMDA, LoRA, IoT, WIFI. The Pasternack log periodic PEANLP1010 can be used for long distance directional communication over a wide range of frequencies.

Log periodic antennas from Pasternack function as boosters where the existing cellular signal is weak and needs to reach further distances. The PEANLP1010 has vertical polarization, 30 horizontal beamwidth, and 27 vertical beamwidth for point to point communication. The included mounting brackets allow for either vertical or horizontal mounting configurations. The directional PEANLP1010 antenna has 1 Type N Female connector on a 9 inches long pigtail.

The 14 dBi max gain log periodic PEANLP1010 antenna operates in 5G bands n48, n77, n78. This 3400 to 3600 MHz 5G directional log periodic antenna with Type N connector is in stock and ready to ship the same day. Contact Pasternack's knowledgeable and friendly technical support and sales staff for your answers on antennas or other products.

Configuration

Design	Log Periodic
Band Type	Single
Radiation Pattern	Directional
Polarization	Vertical
Cable Type	Coax Cable
Cable Length	9.06 in [230.12 mm]
Connector Type	N Female
Number of Ports	1

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain			14	dBi
Front to Back Ratio		16		dB
Input Power			100	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female PEANLP1010](#)



3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female

Antennas Technical Data Sheet

PEANLP1010

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	3.4 to 3.6					GHz
Gain	14					dBi
Horizontal Beam Width	30					Degrees
Vertical Beam Width	27					Degrees
VSWR Max	1.5:1					
Maximum Input Power	100					Watts

Mechanical Specifications

Radome Material

ABS

Size

Overall Length

16.5 in [419.1 mm]

Width

1.5 in [38.1 mm]

Height

3.2 in [81.28 mm]

Weight

0.8 lbs [362.87 g]

Environmental Specifications

Temperature

Operating Range

-40 to +65 deg C

Wind Loading

130.5 MPH [210.02 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female PEANLP1010](#)



3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female

Antennas Technical Data Sheet

PEANLP1010

3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female PEANLP1010](https://www.pasternack.com/single-antenna-0-dbi-gain-n-peanlp1010-p.aspx)


URL: <https://www.pasternack.com/single-antenna-0-dbi-gain-n-peanlp1010-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEANLP1010 CAD Drawing

3400-3600 MHz, 14 dBi, Gain, V-pol, Type N Female

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/21/2022	K.HIETPAS



PE PASTERNAK an INFINITI® brand Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com		THIRD-ANGLE PROJECTION THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED. SHEET 1 OF 1 SCALE N/A	
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: X = ± 2 [508] XX = ± 0.02 [51] XXX = ± 0.005 [13] CABLE LENGTH (L) TOLERANCES: L ≤ 12 [305] = ± 1 [25] / -0 12 [305] < L ≤ 60 [1524] = ± 2 [51] / -0 60 [1524] < L ≤ 120 [3048] = ± 4 [102] / -0 120 [3048] < L ≤ 300 [7620] = ± 6 [152] / -0 300 [7620] < L = +5% / -0 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	SIZE A	CAGE CODE 53919	DRAWN BY K.GLEBOVA
ITEM NO. PEANLP1010		REV A	

NOTES:
1. LABEL PER ILS-100-03 (FOR INTERNAL REFERENCE ONLY)
LABEL LOCATION FOR REFERENCE ONLY

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.