

RP SMA Female to N Female Adapter, VSWR 1.2 up to 6 GHz



PE91734

Configuration

- SMA Female Reverse Polarity Connector 1
- N Female Connector 2
- 50 Ohms Impedance

Features

- Max VSWR of 1.2:1 up to 6 GHz
- Gold over Nickel over Copper Plated Beryllium Copper Contact

Applications

- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE91734 RP SMA female to type N female adapter is part of our full line of RF components available for same-day shipping. Our Reverse Polarity SMA to type N adapter has a female to female gender configuration. PE91734 Reverse Polarity SMA female to type N female adapter operates to 6 GHz. The Pasternack RF adapter provides excellent VSWR of 1.2:1 maximum. This SMA to type N adapter allows for easier connections in tight spaces.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Insertion Loss			0.098	dB
Operating Voltage (AC)			500	Vrms
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size	
Length	1.14 in [28.93 mm]
Width	0.65 in [16.51 mm]
Height	0.65 in [16.51 mm]
Weight	0.09 lbs [38.56 g]

Description	Connector 1	Connector 2
Polarity	Reverse Polarity	
Mating Cycles, Min	100	500

RP SMA Female to N Female Adapter, VSWR 1.2 up to 6 GHz



PE91734

Description	Connector 1	Connector 2
Contact Captivation Axial Force, Min	6.1 lbs [2.77 kg]	6.3 lbs [2.86 kg]
Coupling Proof Torque	5.3 in-lbs [0.6 Nm]	15 in-lbs [1.7 Nm]

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	SMA Female Reverse Polarity		N Female	
Contact	Beryllium Copper	Gold over Nickel over Copper	Beryllium Copper	Gold over Nickel over Copper
Body	Brass	Gold over Nickel over Copper	Brass	Gold over Nickel over Copper

Environmental Specifications

Temperature

Operating Range

-65 to +165 °C

Humidity

MIL-STD-202, Method 206

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

RP SMA Female to N Female Adapter, VSWR 1.2 up to 6 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RP SMA Female to N Female Adapter, VSWR 1.2 up to 6 GHz PE91734](#)

URL: <https://www.pasternack.com/rp-sma-female-to-n-female-adapter-pe91734-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE91734 CAD Drawing

RP SMA Female to N Female Adapter, VSWR 1.2 up to 6 GHz

