

698 to 2700 MHz Omni Antenna 6.5 dBi Gain, 5.5 mm Spring SMA Male Connector, White Fiberglass Radome



Antennas Technical Data Sheet

PEANOM1076

Features

- Heavy Duty 5.5mm Spring Diameter
- Vertically Polarized
- 6.5 dBi Gain
- SMA Male Connector
- 14.75 ft RG58 Cable
- White Fiberglass Radome

Applications

- Offroad/Overland Vehicles
- Mining/Industrial Heavy Equipment
- Commercial Trucking
- Fleet Management
- Farm Equipment

Description

Pasternack's PEANOM1076 is a vertical polarized antenna that ships same day from our ISO 9001:2015 certified facility. The antenna with 698 to 2700 MHz frequency range has a maximum input VSWR of 1.5. This omni directional antenna has SMA male connectors.

This antenna has a white radome made of fiberglass, an overall length of 29.53 in, width of 2 in, and weighs 2.42 lbs. Pasternack's PEANOM1076 is a single band antenna operating from 698 to 2700 MHz with 6.5 dBi gain.

Pasternack's experts are on hand to assist you with any inquiries. Order this PEANOM1076 antenna 7 days a week, 24 hours a day using our on-line ordering system with no MOQs (minimum order quantity) and same-day shipping.

Configuration

Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	FME Male

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	698		2,700	MHz
Input VSWR			1.5:1	
Impedance	50			Ohms
Gain	6.5			dBi
Input Power			100	Watts

Mechanical Specifications

Radome Material	Fiberglass
Size	
Overall Length	29.53 in [750.06 mm]
Width	2 in [50.8 mm]
Height	2 in [50.8 mm]
Weight	2.42 lbs [1.1 kg]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [698 to 2700 MHz Omni Antenna 6.5 dBi Gain, 5.5 mm Spring SMA Male Connector, White Fiberglass Radome PEANOM1076](#)

698 to 2700 MHz Omni Antenna 6.5 dBi Gain, 5.5 mm
Spring SMA Male Connector, White Fiberglass Radome



Antennas Technical Data Sheet

PEANOM1076

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

698 to 2700 MHz Omni Antenna 6.5 dBi Gain, 5.5 mm Spring SMA Male Connector, White Fiberglass Radome from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [698 to 2700 MHz Omni Antenna 6.5 dBi Gain, 5.5 mm Spring SMA Male Connector, White Fiberglass Radome PEANOM1076](#)


URL: <https://www.pasternack.com/698-to-2700-mhz-omni-antenna-6.5-dbi-gain-5.5-mm-spring-sma-male-connector-white-fiberglass-radome-peanom1076-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEANOM1076 CAD Drawing

698 to 2700 MHz Omni Antenna 6.5 dBi Gain, 5.5 mm Spring
SMA Male Connector, White Fiberglass Radome

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	2/28/2023	HBAKIE	KHIETPAS



PASTERNACK an INFINITI® brand		 	INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	REV A									
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES:	<table border="1"> <tr> <td>X = ± 0.2</td><td>[5]</td><td>FRACTIONS</td></tr> <tr> <td>XX = ± 0.2</td><td>[5]</td><td>$\pm 1/32$</td></tr> <tr> <td>XXX = ± 0.05</td><td>[13]</td><td>ANGLES $\pm 1^\circ$</td></tr> </table>	X = ± 0.2	[5]	FRACTIONS	XX = ± 0.2	[5]	$\pm 1/32$	XXX = ± 0.05	[13]	ANGLES $\pm 1^\circ$	CABLE LENGTH TOLERANCES:	SCALE NONE	1 OF 1
X = ± 0.2	[5]	FRACTIONS											
XX = ± 0.2	[5]	$\pm 1/32$											
XXX = ± 0.05	[13]	ANGLES $\pm 1^\circ$											
$\begin{array}{ c c c } \hline & & \\ \hline X & = & \pm 0.2 \\ \hline XX & = & \pm 0.2 \\ \hline XXX & = & \pm 0.05 \\ \hline \end{array}$	$\begin{array}{ c c c } \hline & & \\ \hline [5] & & \\ \hline [5] & & \\ \hline [13] & & \\ \hline \end{array}$	$\begin{array}{ c c c } \hline & & \\ \hline \pm 1/32 & & \\ \hline \pm 1/32 & & \\ \hline \pm 0.05 & & \\ \hline \end{array}$	DESCRIPTION	ITEM NO. PEANOM1076									
		WEBSITE: www.Pasternack.com	PHONE: 1.866.727.8376 1.949.261.1920										
698-2700 MHZ OMNI ANTENNA 6.5 DBI, VEHICLE 5.5 MM SPRING, 14.75 FT RG58 FME MALE 28.75 IN WHITE													
SIZE A	CAGE CODE 53919	DRAWN BY HBAKKE											
ALL DIMENSIONS ARE FOR REFERENCE ONLY. AND SUBJECT TO CHANGE WITHOUT NOTICE.													

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.