



10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna
FAKRA Jack ABS Radome Black IP69K

Antennas Technical Data Sheet

PEANOM1098

Features

- 4 x Cellular 4G/5G
- 5 x Wi-Fi 2.4 GHz / 5 GHz
- 1 x GPS L1 / G1
- MIMO Capable
- Color coded FAKRA Jack
- 17 ft Cable Leads
- Indoor/Outdoor IP69K Rated
- UV Stabilized Black ABS

Applications

- Public Safety
- Emergency Services
- Mobile Base Stations
- Autonomous Vehicles
- Fleet Management
- Smart Cities
- Smart Utilities
- Industrial IoT

Description

The Pasternack PEANOM1098 is a 10-in-1 combination antenna designed for public safety, emergency services, mobile base stations, autonomous vehicles, fleet management, smart cities, smart utilities, or industrial IoT applications. This vertically polarized omnidirectional antenna has color-coded FAKRA female connectors with 17 feet cable leads. Our high-quality mobile antenna with 10 ports has a typical input VSWR of 2:1.

The IoT combination antenna from Pasternack has an overall length of 7 inches, width of 7 inches, and weight of 4 lbs. This PEANOM1098 mobile antenna is IP69K-rated and has a black-colored radome made of UV-stabilized ABS. The 4 cellular, 5 Wi-Fi, 1 GPS combination antenna has an impedance of 50 Ohms and a maximum input power of 10 Watts.

Our vertically polarized mobile antenna can operate at temperatures ranging from -40 to 70 degrees C. This MIMO-capable IoT antenna features four 4G/5G, five 2.4/5 GHz, and one L1/G1 GPS band elements in one radome. Emergency services, first responders, and fleets can rely on our 10-in-1 combination antenna to maintain a secure link between vehicles and dispatch centers.

Configuration

Design	Mobile
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	FAKRA Female
Number of Ports	10

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Input VSWR		2:1		
Impedance		50		Ohms
Input Power			10	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna FAKRA Jack ABS Radome Black IP69K PEANOM1098](#)



10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna FAKRA Jack ABS Radome Black IP69K

Antennas Technical Data Sheet

PEANOM1098

Cellular Specifications					
Frequency Range	617 - 960	1690 - 2700	3300 - 4200	4900 - 6000	MHz
Peak Gain	4	6	7	8	dBi
Port Count	4				
Cable Type	RG58				
Cable Length	17 [5]				
Connector Type	FAKRA Jack				
Connector Color	Bordeaux				
Connector Code	D				
Wi-Fi Specifications					
Frequency Range	2400 - 2500	4900 - 6000			MHz
Peak Gain	5	6			dBi
Port Count	5				
Cable Type	RG58				
Cable Length	17 [5]				
Connector Type	FAKRA Jack				
Connector Color	Beige				
Connector Code	I				
GPS Specifications					
Frequency Range	1562 - 1612				MHz
VSWR	<2.0:1 ± 4 MHz				
LNA Gain	26				dB
Out of band rejection	>40 dB (@ > +/- 100 MHz)				
Typical Noise Figure	≤ 2.7				dB
Notch Filter rejection @787MHz	24				dB
Operating Voltage	3 - 5				VDC
Typical Current	15				mA
Cable Type / Length	RG174 / 17 ft [5 m]				
Connector Type	FAKRA Jack				
Connector Color / Code	Blue / C				

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna FAKRA Jack ABS Radome Black IP69K PEANOM1098](#)



10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna
FAKRA Jack ABS Radome Black IP69K

Antennas Technical Data Sheet

PEANOM1098

Mechanical Specifications

Radome Material

UV Stabilized ABS

Size

Overall Length

7 in [177.8 mm]

Width

7 in [177.8 mm]

Height

3.15 in [80.01 mm]

Weight

4 lbs [1.81 kg]

Environmental Specifications

Temperature

Operating Range

-40 to +70 deg C

Ingress Protection

IP69K

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna FAKRA Jack ABS Radome Black IP69K from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna FAKRA Jack ABS Radome Black IP69K PEANOM1098](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

10-in-1 Cellular, Wi-Fi, GPS Combination IoT Antenna
FAKRA Jack ABS Radome Black IP69K

ZONE		REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
		A	INITIAL RELEASE	03/23/2023	KGLEBOVA	KHIETPAS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		PE PASTERNAK® an INFINITI® brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5																				
TOLERANCES: <table border="0"> <tr> <td>X = ±.2</td> <td>[.5]</td> <td>FRACTIONS</td> </tr> <tr> <td>.XX = ±.02</td> <td>[.5]</td> <td>± 1/32</td> </tr> <tr> <td>.XXX = ±.005</td> <td>[.13]</td> <td>ANGLES ±°</td> </tr> </table>		X = ±.2	[.5]	FRACTIONS	.XX = ±.02	[.5]	± 1/32	.XXX = ±.005	[.13]	ANGLES ±°	CABLE LENGTH TOLERANCES: <table border="0"> <tr> <td>≤ 12 [305]</td> <td>± .1 [25] / -0</td> </tr> <tr> <td>> 12 [305] ≤ 60 [1524]</td> <td>± .2 [51] / -0</td> </tr> <tr> <td>> 60 [1524] ≤ 120 [3048]</td> <td>± .4 [102] / -0</td> </tr> <tr> <td>> 120 [3048] ≤ 300 [7620]</td> <td>± .6 [152] / -0</td> </tr> <tr> <td>> 300 [7620]</td> <td>± .5% / -0</td> </tr> </table>		≤ 12 [305]	± .1 [25] / -0	> 12 [305] ≤ 60 [1524]	± .2 [51] / -0	> 60 [1524] ≤ 120 [3048]	± .4 [102] / -0	> 120 [3048] ≤ 300 [7620]	± .6 [152] / -0	> 300 [7620]	± .5% / -0	SCALE NONE SHEET 1 OF 1	
X = ±.2	[.5]	FRACTIONS																						
.XX = ±.02	[.5]	± 1/32																						
.XXX = ±.005	[.13]	ANGLES ±°																						
≤ 12 [305]	± .1 [25] / -0																							
> 12 [305] ≤ 60 [1524]	± .2 [51] / -0																							
> 60 [1524] ≤ 120 [3048]	± .4 [102] / -0																							
> 120 [3048] ≤ 300 [7620]	± .6 [152] / -0																							
> 300 [7620]	± .5% / -0																							
WEBSITE: www.Pasternack.com PHONE: 1.866.727.8376 1.949.261.1920		DESCRIPTION 4 CELLULAR, 5 WI-FI, 1 GPS COMBINATION ANTENNA FAKRA FEMALE BLACK		ITEM NO. PEANOM1098																				
SIZE A		CAGE CODE 53919		DRAWN BY KGLEBOVA																				
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.																								