



136-940MHz, 4.5 dBi Gain, Omni-directional Antenna
with Magnetic NMO Mount, N-Female Connector

Antennas Technical Data Sheet

PEANMOB1003-NF

Features

- Outdoor Rated Omni Directional Antenna
- 4.5 dBi Gain
- Easy to install magnetic mount offering temporary plug and play installation
- NMO Magnetic Mount, Black ABS Radome
- 1.5:1 VSWR Max
- 10 Foot, Black Low-Loss LMR195 Equivalent Cable
- N-Female Connector

Applications

- Offroad/Overland Vehicles
- Mining/Industrial
- Heavy Equipment
- Commercial Trucking
- Fleet Management
- Farm Equipment

Description

The PEANMOB1003-NF from Pasternack is an omnidirectional antenna with a 4.5 dBi gain that transmits high-power signals and faster speed. This in-building antenna comes with a magnetic NMO mount specifically designed for high-performance applications. Our high-quality omni antenna is available in black color and can be procured with no order limit. This vertically polarized antenna has a frequency range of 136 to 940 MHz, which is ideal for indoor low-profile, in-building, and mobile applications.

The NMO-type magnetic mount on Pasternack's PEANMOB1003-NF omnidirectional antenna makes it an ideal solution when the portability of the antenna is needed. This NMO antenna mount is constructed with a heavy-duty magnet to ensure secure mounting. The magnetic base allows a temporary plug-and-play installation. No drilling is required for the installation of this antenna mount, making it easy to fine-tune the antenna location. This magnetic mount has an N-type female connector and can be used for WLAN, Wi-Fi, public safety, and mobile RF applications.

Pasternack has one of the largest in-stock selections of omnidirectional in-building antennas with the same-day shipment. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal vertically polarized antenna with a magnetic NMO mount for your requirements.

Configuration

Design	Omni
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	N Female
Number of Ports	1

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	136		940	MHz
Input VSWR			1.5:1	
Gain		4.5		dBi
Input Power			30	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [136-940MHz, 4.5 dBi Gain, Omni-directional Antenna with Magnetic NMO Mount, N-Female Connector PEANMOB1003-NF](#)



136-940MHz, 4.5 dBi Gain, Omni-directional Antenna
with Magnetic NMO Mount, N-Female Connector

Antennas Technical Data Sheet

PEANMOB1003-NF

Mechanical Specifications

Radome Material

Stainless Steel

Size

Overall Length

4.74 in [120.4 mm]

Width

3 in [76.2 mm]

Height

3 in [76.2 mm]

Weight

1.8 lbs [816.47 g]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

136-940MHz, 4.5 dBi Gain, Omni-directional Antenna with Magnetic NMO Mount, N-Female Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [136-940MHz, 4.5 dBi Gain, Omni-directional Antenna with Magnetic NMO Mount, N-Female Connector PEANMOB1003-NF](#)

URL: <https://www.pasternack.com/136-940mhz-4.5-dbi-gain-omni-directional-antenna-with-magnetic-nmo-mount-n-female-connector-peanmob1003-nf-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEANMOB1003-NF CAD Drawing

136-940MHz, 4.5 dBi Gain, Omni-directional Antenna with
Magnetic NMO Mount, N-Female Connector

F E D C B A

F E D C B A

Ø 3.0
[76]

N FEMALE
CONNECTOR

OMNI
ANTENNA

4.7
[118]

3.7
[93]

10 FOOT LENGTH
195 SERIES BLACK
COAX CABLE

NMO MAGNETIC
BASE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.


T-Rev 02

REVISION			
ZONE	REV.	DESCRIPTION	DATE
	A	INITIAL RELEASE	02/27/2023

CHANGED BY	APPROVED BY
BPUCHASKI	KHIETPAS



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920



INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5
SCALE NONE
SHEET 1 OF 1

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
.X = ± .2 [.5] FRACTIONS
.XX = ± .02 [.5] ± 1/32
.XXX = ± .005 [.13] ANGLES ± 1°
CABLE LENGTH TOLERANCES:
≤ 12 [305] = +1 [25] / -0
> 12 [305] ≤ 60 [1524] = +2 [51] / -0
> 60 [1524] ≤ 120 [3048] = +4 [102] / -0
> 120 [3048] ≤ 300 [7620] = +6 [152] / -0
> 300 [7620] = +5% / -0

DESCRIPTION			
VHF, UHF, 4G Omni Antenna 4.5 dBi, Vehicle NMO, Black N-Female Connector			
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	53919	BPUCHASKI	PEANMOB1003-NF
			REV
			A