

136 to 174 MHz Omni Antenna 4.5 dBi Gain,
NMO Connector, Stainless Steel

Antennas Technical Data Sheet

PEANOM1084

Features

- Vertically Polarized
- 4.5 dBi Gain
- NMO Connector
- Stainless Steel
- 1.5:1 VSWR Max
- 50 Watt Max Input Power
- Tunable Frequency

Applications

- Offroad/Overland Vehicles
- Mining/Industrial Heavy Equipment
- Commercial Trucking
- Fleet Management
- Farm Equipment

Description

Pasternack's PEANOM1084 is a vertical polarized antenna that ships same day from our ISO 9001:2015 certified facility. The antenna with 136 to 174 MHz frequency range has a maximum input VSWR of 1.5. This omni directional antenna has NMO male connectors.

This antenna is made of stainless steel, an overall length of 53.54 in, width of 2 in, and weighs 0.66 lbs. Pasternack's PEANOM1084 is a single band antenna operating from 136 to 174 MHz with 4.5 dBi gain.

Pasternack's experts are on hand to assist you with any inquiries. Order this PEANOM1084 antenna 7 days a week, 24 hours a day using our on-line ordering system with no MOQs (minimum order quantity) and same-day shipping.

Configuration

Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	NMO

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range (Tunable)	136		174	MHz
Operational Bandwidth		5		MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		4.5		dBi
Input Power			50	Watts


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [136 to 174 MHz Omni Antenna 4.5 dBi Gain, NMO Connector, Stainless Steel PEANOM1084](#)

136 to 174 MHz Omni Antenna 4.5 dBi Gain,
NMO Connector, Stainless Steel

Antennas Technical Data Sheet

PEANOM1084

CUTTING CHART



Mechanical Specifications

Radome Material

Stainless Steel

Size

Overall Length

53.54 in [135.99 cm]

Width

2 in [50.8 mm]

Height

2 in [50.8 mm]

Weight

0.66 lbs [299.37 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [136 to 174 MHz Omni Antenna 4.5 dBi Gain, NMO Connector, Stainless Steel PEANOM1084](#)

136 to 174 MHz Omni Antenna 4.5 dBi Gain,
NMO Connector, Stainless Steel

Antennas Technical Data Sheet

PEANOM1084

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

1: Loosen Screw, Sperate Whip and Base.

2: Find whip length of correct frequency according to cutting chart.

3: Measure the length of the steel whip and cut it from bottom side without cap.

4: Re-fix the steel whip and the base with screws.

136 to 174 MHz Omni Antenna 4.5 dBi Gain, NMO Connector, Stainless Steel from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [136 to 174 MHz Omni Antenna 4.5 dBi Gain, NMO Connector, Stainless Steel PEANOM1084](#)

URL: <https://www.pasternack.com/136-to-174-mhz-omni-antenna-4.5-dbi-gain-nmo-connector-stainless-steel-reflector-peanom1084-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEANOM1084 CAD Drawing

136 to 174 MHz Omni Antenna 4.5 dBi Gain, NMO Connector, Stainless Steel

