

2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole,  
90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain



## Antennas Technical Data Sheet

**PEANRBD1043**

### Features

- 2400-2500 / 5150-5850 MHz, 1.2 / 4.26 dBi Gain
- 90-degree RP-SMA male connector
- Plug and play
- VSWR < 2.5:1
- Linear polarization
- Monopole antenna

### Applications

- 2.4/5 GHz Wi-Fi and ISM applications
- WLAN applications
- IOT, Wireless audio/video systems
- Home automation
- Telemetry, remote monitoring
- Wireless data acquisition
- 802.11 a/b/g/n/ax/ac, wireless hotspots
- PtP and PtMP applications
- 5G bands: n46, n53
- 4G LTE bands: B252, B255, B46

### Description

The Pasternack PEANRBD1043 WiFi antenna is an omni antenna operating from 2.4 GHz to 5.85 GHz with 1.2 and 4.26 dBi gain. Our high-quality rubber duck antenna transmits high power signals, increasing the signal strength, thus providing improved coverage, better broadcast control, and faster speed. The RP-SMA male connector on this monopole antenna enables it to be used vertically, at a right angle, or at any angle in between.

This PEANRBD1043 WiFi antenna is 0.7 inches wide, 4.33 inches long, and 0.7 inches tall. Pasternack's omnidirectional antenna has a maximum input VSWR of 2.5:1, which results in the best power transfer and reduced losses. This omnidirectional antenna has a linear polarization, an RP-SMA male connector, and an TPEE radome material. Our black WiFi antenna functions between -40 to 65 degrees C and has 50 Ohm impedance.

The Pasternack WiFi antenna is ideal for 2.4/5 GHz Wi-Fi and ISM applications, WLAN, Bluetooth, IOT, wireless audio/video systems, home automation, telemetry, remote monitoring, wireless data acquisition, 802.11 a/b/g/n/ax, wireless hotspots, PtP and PtMP applications. This monopole antenna has a waterproof design, a high power handling capacity, and IP66 ingress protection rating. The double band antenna has a gain of 1.2 dBi for the 2.4 GHz to 2.5 GHz frequency range and a gain of 4.26 dBi for the 5.15 GHz to 5.85 GHz frequency range.

This 1.2 dBi gain omni directional antenna is one of the thousands of products available from Pasternack's in-stock inventory with same business day shipment for local, domestic, and international orders. Make your online purchase for our high-quality antennas and take advantage of the same business day shipping services. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect 2.4 GHz to 5.85 GHz antenna for your requirement.

### Configuration

Design	Rubber Duck
Band Type	Multi
Radiation Pattern	Omni Directional
Polarization	Linear
Connector Type	SMA Male Reverse Polarity

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2,400		5,850	MHz
Input VSWR			2.5:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole, 90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain PEANRBD1043](#)

2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole,  
90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain



## Antennas Technical Data Sheet

**PEANRBD1043**

Impedance	50	Ohms
Input Power	10	Watts

### Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.4 to 2.5	5.15 to 5.85				GHz
Gain	1.25	4.26				dBi

### Mechanical Specifications

Radome Material

TPEE

#### Size

Overall Length

4.33 in [109.98 mm]

Width

0.7 in [17.78 mm]

Height

0.7 in [17.78 mm]

Weight

0.0242 lbs [10.98 g]

### Environmental Specifications

#### Temperature

-40 to +65 deg C

Operating Range

-40 to +80 deg C

Storage Range

#### Environment

Waterproof

Ingress Protection

IP66

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole, 90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain PEANRBD1043](#)

2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole,  
90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain



## Antennas Technical Data Sheet

**PEANRBD1043**

2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole, 90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole, 90-degree angle, RPSMA Male Connector, 1.2 and 4.26 dBi Gain PEANRBD1043](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PEANRBD1043 CAD Drawing

2.4 GHz to 5.85 GHz Dual Band Antenna, Monopole, 90-degree angle,  
RPSMA Male Connector, 1.2 and 4.26 dBi Gain

