



## 5150-5825 MHz, 5.1 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX Connector

### Antennas Technical Data Sheet

**PESMA1015**

#### Features

- High Efficiency
- Isotropic radiation patterns
- Linear polarization
- Ultra-Compact design
- Low loss material

- Extended operating temperatures
- Case mounting or on board mount
- Frequency stabilization
- IPEX connector - 80mm cable
- Single piece for easy buy

#### Applications

- IoT, M2M, Telemetry
- Wireless Remote Control
- Personal Area Networks(PAN)
- Industrial/Commercial Equipment
- 2.4/5 GHz - Wi-Fi/BT/BLE/ZigBee/ISM applications

- IEEE 802.11 a/n/ac/ax embedded applications
- Remote Technology / Monitoring
- Consumer Tracking
- Smart Home / Wearables / Devices
- Agriculture, healthcare, digital signage

#### Description

Linear polarized antenna PESMA1015 from Pasternack is part of our extensive in-stock omni directional antennas that ship the same day from our ISO 9001:2015 certified facility. The stamped metal antenna has a maximum frequency of 5825 MHz and a minimum frequency of 5150 MHz. This stamped metal antenna with an IPEX connector has a maximum input VSWR of 2:1.

This stamped metal antenna with an IPEX connector has an overall length of 1.18 inches and a width of 0.39 inches. Pasternack's PESMA1015 is a single band antenna operating from 5150 to 5825 MHz with a 5.1 dBi gain. Our high-quality omni directional antenna has an impedance of 50 Ohms.

Pasternack's experts are on hand to assist you with any inquiries. Order this PESMA1015 stamped metal antenna 7 days a week, 24 hours a day, using our on-line ordering system with no MOQs (minimum order quantity) and same-day shipping. Our knowledgeable sales team and ability in the global availability market allow us to lead the industry in supplying RF products like these omni directional antennas.

#### Configuration

|                   |                    |
|-------------------|--------------------|
| Design            | Stamped Metal      |
| Band Type         | Single             |
| Radiation Pattern | Omni Directional   |
| Polarization      | Linear             |
| Cable Length      | 3.15 in [80.01 mm] |
| Connector Type    | IPEX               |
| Number of Ports   | 1                  |

#### Electrical Specifications

| Description     | Minimum | Typical | Maximum | Units |
|-----------------|---------|---------|---------|-------|
| Frequency Range | 5,150   |         | 5,825   | MHz   |
| Input VSWR      |         |         | 2:1     |       |
| Impedance       |         | 50      |         | Ohms  |
| Gain            |         | 5.1     |         | dBi   |
| Input Power     |         |         | 1       | Watt  |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [5150-5825 MHz, 5.1 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX Connector PESMA1015](#)

5150-5825 MHz, 5.1 dBi, Stamped Metal AP/Router  
Embedded Antenna With IPEX Connector



## Antennas Technical Data Sheet

**PESMA1015**

### Mechanical Specifications

#### Size

Overall Length  
Width  
Height

1.18 in [29.97 mm]  
0.39 in [9.91 mm]  
0.22 in [5.59 mm]

### Environmental Specifications

#### Temperature

Operating Range

-40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

5150-5825 MHz, 5.1 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [5150-5825 MHz, 5.1 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX Connector PESMA1015](#)

URL: <https://www.pasternack.com/5.1-stamped-metal-antenna-5150-5825-mhz-invalid-alias-lookup-for-ipex-connector-pesma1015-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PESMA1015 CAD Drawing

5150-5825 MHz, 5.1 dBi, Stamped Metal AP/Router

Embedded Antenna With IPEX Connector

F E D C B A

