

## 460 MHz, Gooseneck Antenna, SMA Female Connector



### PEANOM1154

#### Features

- 460 MHz Operating Frequency
- Flexible Gooseneck
- SMA Female Connector
- 1.5:1 VSWR
- 10 Watt Max Input Power
- Typical 3 dBi Gain

#### Applications

- Unmanned Vehicles
- Manpack Radio Systems
- Secure Communications
- Surveillance Systems
- Mobile Systems

#### Description

The PEANOM1154 from Pasternack is an omnidirectional gooseneck antenna that features a flexible gooseneck mounting base. This flexible antenna can be bent and repositioned at any angle, allowing users to optimize signal reception and transmission in any environment. Our single-band gooseneck antenna with vertical polarization can operate at a minimum frequency of 400 MHz, a center frequency of 460 MHz, and a maximum frequency of 520 MHz.

Pasternack's PEANOM1154 gooseneck antenna has an impedance of 50 Ohms and a maximum input power of 10 Watts. This omnidirectional antenna is designed to withstand temperatures ranging from -40 to 80 degrees C. Our vertical polarized antenna has an overall length of 12.4 inches, a width of 1.5 inches, and a weight of 0.33 lbs. This gooseneck antenna is lightweight and compact, making it easy to transport and deploy in the field.

This vertically polarized antenna has a maximum input VSWR of 1.5:1. Our single-band gooseneck antenna with an SMA female connector has a nominal gain of 3 dBi. This PEANOM1154 antenna comes with a black TPE radome that offers a protective covering without compromising the antenna system's performance.

#### Configuration

Design	Gooseneck
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	SMA Female

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	400		520	MHz
Center Frequency		460		MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		3		dBi
Input Power			10	Watts

#### Mechanical Specifications

Radome Material	TPE
-----------------	-----

## 460 MHz, Gooseneck Antenna, SMA Female Connector

**PEANOM1154****Size**

Length	13 in [330.2 mm]
Width	1.5 in [38.1 mm]
Height	1.5 in [38.1 mm]
Weight	0.5 lbs [226.8 g]

**Environmental Specifications****Temperature**

Operating Range

-40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)**Plotted and Other Data**

Notes:

**Typical Radiation Pattern****Appendix****Electrical Downtilt:** Angle in the antenna's elevation pattern in which the maximum gain occurs.**Gain:** Antenna's average gain.**Front to Back Ratio @ 180°±30°:** Average difference between the antenna's maximum gain and the maximum gain in the antenna's back lobe over  $\pm 30^\circ$  angles.**Cross-polarization Ratio (dB):** Typical difference between the co-polarization and cross-polarization gain across the sector's 3 dB Beam Width.

460 MHz, Gooseneck Antenna, SMA Female Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [460 MHz, Gooseneck Antenna, SMA Female Connector PEANOM1154](#)URL: <https://www.pasternack.com/3-dbi-gooseneck-antenna-400-520-mhz-sma-female-connector-peanom1154.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PEANOM1154 CAD Drawing

460 MHz, Gooseneck Antenna, SMA Female Connector

