

Broadband Gain Horn Antenna, 6 GHz to 67 GHz
13 dBi Gain, 1.85mm Female Connector

Specialty Waveguide Antennas Technical Data Sheet

PEWAN1160

Features

- Antenna Measurements
- Laboratory Use
- Microwave Testing
- Radome Testing
- EMC measurement
- Satellite Antenna Testing
- Radar Cross Section

Applications

- Ultra Broadband 6 GHz to 67 GHz
- Double-Ridge Waveguide
- Linearly Polarized
- 13 dBi Nominal Gain
- 1.85mm Female Connector
- Mounting Bracket Included
- Powder Coated Aluminum

Description

The PEWAN1160 broadband gain horn antenna (double ridge waveguide horn) from Pasternack is part of our comprehensive selection of waveguide antennas. This broadband horn features an 1.85mm Female coaxial connector and operates from 6 to 67 GHz.

Our PEWAN1160 broadband gain horn antenna has a nominal gain of 13 dBi with a typical input VSWR of 1.5:1. Pasternack's double-ridge broadband horns are available in 10, 11, 13, 15, and 20 dBi models with varying cross band frequency ranges to suit all application needs.

Waveguide antennas, such as the PEWAN1160 are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our double ridge waveguide antennas with 1.85mm Female interface are part of over 40,000 RF, microwave, and millimeter wave components from Pasternack available worldwide and Ship same day.


Configuration

Pattern	Directional
Polarization	Linear
Antenna Design Type	Broadband Gain Horn
RF Connector	1.85mm Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	6		67	GHz
Nominal Gain		13		dBi
VSWR		1.5:1		

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector PEWAN1160](#)



Broadband Gain Horn Antenna, 6 GHz to 67 GHz
13 dBi Gain, 1.85mm Female Connector

Specialty Waveguide Antennas Technical Data Sheet

PEWAN1160

Mechanical Specifications

Size

Length 2.55 in [64.77 mm]

Width 1.27 in [32.26 mm]

Height 1.09 in [27.69 mm]

Weight 0.05 lbs [22.68 g]

Body Material and Plating Aluminum, Powder Coat
RF Connector 1.85mm Female


Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector PEWAN1160](#)




Broadband Gain Horn Antenna, 6 GHz to 67 GHz
13 dBi Gain, 1.85mm Female Connector


Specialty Waveguide Antennas Technical Data Sheet

PEWAN1160

Typical Performance Data






Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector PEWAN1160](#)




Broadband Gain Horn Antenna, 6 GHz to 67 GHz
13 dBi Gain, 1.85mm Female Connector

Specialty Waveguide Antennas Technical Data Sheet

PEWAN1160




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector PEWAN1160](#)




Broadband Gain Horn Antenna, 6 GHz to 67 GHz
13 dBi Gain, 1.85mm Female Connector

Specialty Waveguide Antennas Technical Data Sheet

PEWAN1160



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector PEWAN1160](#)



Broadband Gain Horn Antenna, 6 GHz to 67 GHz
13 dBi Gain, 1.85mm Female Connector

Specialty Waveguide Antennas Technical Data Sheet

PEWAN1160

Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Broadband Gain Horn Antenna, 6 GHz to 67 GHz 13 dBi Gain, 1.85mm Female Connector PEWAN1160](https://www.pasternack.com/waveguide-horn-antenna-67-ghz-13-dbi-1.85mm-female-pewan1160-p.aspx)

URL: <https://www.pasternack.com/waveguide-horn-antenna-67-ghz-13-dbi-1.85mm-female-pewan1160-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

