



Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna

TECHNICAL DATA SHEET

PEMARRM02

Features

- Stainless steel marine grade mount
- Dual swivel ratchet style
- 1"-14 male threaded
- Heavy duty

- Mirror polish
- Anti corrosion material
- Flat base fixture

Applications

- Marine antenna mounts
- Marine communication: VHF, GPS, satellite phones
- Navigation: Radar, sonar, depth finders

- Fishing: Fish finders, sonar-based equipment
- Entertainment: Satellite TV, radio systems
- Emergency services: Search and rescue operations

Description

The Pasternack PEMARRM02 dual swivel ratchet style antenna mount is offered for marine and omnidirectional antennas. This marine antenna mount is constructed of anti-corrosion stainless steel with a mirror polish. Our heavy-duty mount is ideal for marine communication, fishing, navigation, entertainment, and emergency services.

The working temperature range for our dual swivel ratchet-style installation is -40 to 80 degrees Celsius. The PEMARRM02 marine antenna mount from Pasternack is available in 8-inch length, 2.52-inch width, and 5.5-inch height. This antenna mount has a flat base fixture and 1"-14 male threads, making it suited for use with search and rescue equipment, satellite TV, radio systems, radar, sonar, depth finders, VHF, GPS, satellite phones, fish finders, and sonar-based equipment applications.

Pasternack has one of the largest in-stock selections of marine grade dual swivel ratchet style antenna mounts for international and domestic orders. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect stainless steel marine antenna mount for your requirements.

Mechanical Specifications

Size

Length

8 in [203.2 mm]

Width

2.52 in [64.01 mm]

Height

5.5 in [139.7 mm]

Weight

1.32 lbs [598.74 g]

Environmental Specifications

Operating Temperature, Min

-40 deg C

Operating Temperature, Max

80 deg C

Material

Stainless Steel

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna](#)



Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna

TECHNICAL DATA SHEET

PEMARRM02

Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

CAD Drawing

E Casting Heavy Duty 4-way Ratchet Marine mount with
Standard 1"-14 male threads for marine antenna

