

## Standard Gain Horn Cage Style Antenna Mount, Waveguide Size WR159, IEC R58



### Waveguide Antenna Accessories Technical Data Sheet

**PEWAN159-MNT**

#### Features

- Supports WR159 waveguide size
- Supports flange type: UG-1730/U, UG-1731/U, UDR 58, CPR 159, RDR 58, PDR 58, UG-1354/U, UG-1355/U
- All Aluminum material
- Chromate conversion - inside finish
- Anti corrosion grey paint - outside finish
- Easy mount option and Seamless fit

#### Applications

- Gain Horn or Waveguide Mounting
- Antenna Measurements
- Laboratory use
- Microwave Testing
- Radome Testing
- EMC measurement
- Satellite Antenna Testing

#### Description

Pasternack's PEWAN159-MNT is an antenna mount specifically designed for gain horn antennas. This antenna mount is built with a waveguide size of WR159 and is compatible with the IEC R58 standard which ensures seamless integration with various equipment. Our high-quality WR159 gain horn antenna mount is suitable for test and measurement applications. This antenna holder from Pasternack weighs 0.87 pounds which makes it highly portable and easy to handle.

The PEWAN159-MNT antenna mount is available with 4.33 inches of length and a height of 2.76 inches. Our IEC R58 gain horn antenna holder has an aluminum body with chromate conversion inside finish, providing protection against environmental factors. This WR159 mount is coated with an anticorrosion gray paint, safeguarding it from moisture and UV radiation. Additional dimensions and specifications for this WR159 gain horn antenna mount are on our downloadable PDF datasheet above.

This gain horn antenna mount is one of the thousands of products available from Pasternack's in-stock inventory with same business day shipment for local, domestic, and international orders. Make your online purchase for our high-quality IEC R58 standard antenna mount and take advantage of the same business day shipping services. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect WR159 gain horn antenna mount for your requirement.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Standard Gain Horn Cage Style Antenna Mount, Waveguide Size WR159, IEC R58 PE-WAN159-MNT](#)

## Standard Gain Horn Cage Style Antenna Mount, Waveguide Size WR159, IEC R58



### Waveguide Antenna Accessories Technical Data Sheet

**PEWAN159-MNT**

#### Mechanical Specifications

Body Material	Aluminum
Body Finish	Chromate conversion
Length	4.330709 in [110 mm]
Width	4.330709 in [110 mm]
Height	2.755906 in [70 mm]
Weight	0.865 lbs [392.36 g]

#### Compliance Certifications (see [product page](#) for current document)

Standard Gain Horn Cage Style Antenna Mount, Waveguide Size WR159, IEC R58 from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Standard Gain Horn Cage Style Antenna Mount, Waveguide Size WR159, IEC R58 PEWAN159-MNT](#)


URL: <https://www.pasternack.com/standard-gain-horn-cage-style-antenna-mount-waveguide-size-wr159-iec-r58-pewan159-mnt-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.


PEWAN159-MNT CAD Drawing

Standard Gain Horn Cage Style Antenna Mount, Waveguide Size WR159, IEC R58


ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
A		INITIAL RELEASE	05/01/2023	AKRESOWSKI	KHIETPAS




— ANTENNA MOUNTING PLATE  
✓ 4X STANDOFF  
✓ LOWER PLATE



## ANTENNA MOUNTING PLATE DETAIL



## LOWER PLATE DETAIL



**PE PASTERNAK**  
an INFINITI® brand

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

NS ANTENNA MOULERNACK.COM | 1.949.261.1920

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.  
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EMBARGO CONTROLS, ETC., OF THE UNITED STATES GOVERNMENT. DIVISIONS OF INFINITE ELECTRONICS, INC. LOCATED

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS  
TOLENCES

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5		REV A
SCALE	Sheet	
1 OF 1		
NONE		
DESCRIPTION		
S12 [305] = +1 [25] / -0		
>12 [305] = 60 [1524] = +2 [51] / -0		
>60 [1524] = 120 [3048] = +4 [102] / -0		
>120 [3048] = 300 [7620] = +6 [152] / -0		
>300 [7620] = +8% / -0		
SIZE	CAGE CODE	DRAWN BY
A	53919	AKRESOWSKI
ITEM NO.	PEWAN159-MNT	

10