

WR-430 Standard Gain Horn with 20 dBi gain, N Female connector

Technical Data Sheet

PEWAN430-20NF

Features

- 1.7 GHz to 2.6 GHz
- WR-430 Waveguide Band
- 20 dBi Nominal Gain
- N Female Connector

Applications

• Antenna Measurements	• Microwave Radio Systems
• Wireless Communication	• Radome Testing
• Laboratory Use	• Automotive Antenna Test

Solutions
• Radar Cross Section
• Satellite Antenna Testing

Description

The PEWAN430-20NF standard gain horn antenna (also known as waveguide horn) from Pasternack is part of our comprehensive selection of waveguide antennas. This standard gain horn is mated with a WR-430 to N Female waveguide to coaxial adapter and operates from 1.7 GHz to 2.6 GHz.

Our PEWAN430-20NF standard gain horn antenna has a nominal gain of 20 dBi with a Horizontal and Vertical HPBW (Half Power Beam Width) of 17.5 dB and 17.3 dB respectively. Pasternack's N Female to WR-430 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and connectorized input.

Waveguide antennas, such as the PEWAN430-20NF are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our WR-430 waveguide antennas with N Female interface is part of over 40,000 RF, microwave and millimeter wave components from Pasternack available worldwide and Ship same day.

Configuration


Design	WR-430 Standard Gain Horn
Coaxial Interface	N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	1.7		2.6	GHz
Waveguide Standard Gain Horn				
Gain		20		dBi
Horizontal Half Power Beam Width		17.5		Degrees
Vertical Half Power Beam Width		17.3		Degrees
Waveguide to Coaxial Adapter				
Input VSWR			1.3:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-430 Standard Gain Horn with 20 dBi gain, N Female connector PEWAN430-20NF](#)

WR-430 Standard Gain Horn with 20 dBi
gain, N Female connector



Technical Data Sheet

PEWAN430-20NF

Mechanical Specifications

Size

Length

47.004 in [119.39 cm]

Width

21.027 in [534.09 mm]

Height

15.6 in [396.24 mm]

Weight

16.9522 lbs [7.69 kg]

RF Connector

Type

N Female

Waveguide Interface

Waveguide Size

WR-430


Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-430 Standard Gain Horn with 20 dBi gain, N Female connector PEWAN430-20NF](#)




WR-430 Standard Gain Horn with 20 dBi
gain, N Female connector


Technical Data Sheet

PEWAN430-20NF

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-430 Standard Gain Horn with 20 dBi gain, N Female connector PEWAN430-20NF](#)




WR-430 Standard Gain Horn with 20 dBi
gain, N Female connector

Technical Data Sheet

PEWAN430-20NF




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-430 Standard Gain Horn with 20 dBi gain, N Female connector PEWAN430-20NF](#)



WR-430 Standard Gain Horn with 20 dBi
gain, N Female connector

Technical Data Sheet

PEWAN430-20NF




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-430 Standard Gain Horn with 20 dBi gain, N Female connector PEWAN430-20NF](#)



WR-430 Standard Gain Horn with 20 dBi gain, N Female connector

Technical Data Sheet

PEWAN430-20NF



WR-430 Standard Gain Horn with 20 dBi gain, N Female connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-430 Standard Gain Horn with 20 dBi gain, N Female connector PEWAN430-20NF](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWAN430-20NF CAD Drawing

WR-430 Standard Gain Horn with 20 dBi gain, N Female connector

