

# 2412-2484/ 5150- 5825 MHz, 0.5/3.5 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX-50 Pack



## Antennas Technical Data Sheet

**PESMA1014-50PK**

### Features

- High Efficiency
- Isotropic radiation patterns
- Linear polarization
- Ultra-Compact design
- Low loss material
- Extended operating temperatures

- Case mounting or on board mount
- Dual band frequency stabilization
- IPEX connector - 110mm cable
- 50-pack for easy buy

### Applications

- IoT, M2M, Telemetry
- Wireless Remote Control
- Personal Area Networks(PAN)
- Industrial/Commercial Equipment
- 2.4/5 GHz - Wi-Fi/BT/BLE/ZigBee/ISM applications

- IEEE802.11a/b/g/n/ac embedded applications
- Remote Technology / Monitoring
- Consumer Tracking
- Smart Home / Wearables / Devices
- Agriculture, healthcare, digital signage

### Description

Linear polarized antenna PESMA1014-50PK from Pasternack is part of our extensive in-stock omni directional antennas that ship the same day from our ISO 9001:2015 certified facility. The stamped metal antenna with an IPEX connector has a maximum frequency of 5825 MHz and a minimum frequency of 2412 MHz. This 50-pack stamped metal antenna has a maximum input VSWR of 2:1.

This stamped metal antenna with an IPEX connector has an overall length of 1.73 inches and a width of 0.37 inches. Pasternack's PESMA1014-50PK is a dual band antenna operating from 2412 to 2484 MHz with 0.5 dBi gain and 5150 to 5825 MHz with 3.5 dBi gain. Our high-quality 50-pack omni directional antenna has an impedance of 50 Ohms.

Pasternack's experts are on hand to assist you with any inquiries. Order this PESMA1014-50PK 50-pack stamped metal antenna 7 days a week, 24 hours a day, using our on-line ordering system with no MOQs (minimum order quantity) and same-day shipping. Our knowledgeable sales team and ability in the global availability market allow us to lead the industry in supplying RF products like these omni directional antennas.

### Configuration

Design	Stamped Metal
Band Type	Dual
Radiation Pattern	Omni Directional
Polarization	Linear
Cable Length	4.3 in [109.22 mm]
Connector Type	IPEX

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2,412		5,825	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain	0.5		3.5	dBi
Input Power			1	Watt

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2412-2484/ 5150- 5825 MHz, 0.5/3.5 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX-50 Pack PESMA1014-50PK](#)

2412-2484/ 5150- 5825 MHz, 0.5/3.5 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX-50 Pack



## Antennas Technical Data Sheet

**PESMA1014-50PK**

### Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.412 to 2.484	5.15 to 5.825				GHz
Gain	0.5	3.5				dBi

### Mechanical Specifications

#### Size

Overall Length

1.73 in [43.94 mm]

Width

0.37 in [9.4 mm]

Height

0.2 in [5.08 mm]

### Environmental Specifications

#### Temperature

Operating Range

-40 to +85 deg C

### Compliance Certifications

(see [product page](#) for current document)

### Plotted and Other Data

Notes:

2412-2484/ 5150- 5825 MHz, 0.5/3.5 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX-50 Pack from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2412-2484/ 5150- 5825 MHz, 0.5/3.5 dBi, Stamped Metal AP/Router Embedded Antenna With IPEX-50 Pack PESMA1014-50PK](#)

URL: <https://www.pasternack.com/0.5-dual-band-stamped-metal-antenna-2412-5825-mhz-invalid-alias-lookup-for-ipex-connector-pesma1014-50pk-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PESMA1014-50PK CAD Drawing

2412-2484/ 5150- 5825 MHz, 0.5/3.5 dBi, Stamped Metal AP/

Router Embedded Antenna With IPEx-50 Pack

F E D C B A



<b>PASTERNACK®</b> an INFINIT® brand	
INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
SCALE	NONE
SHEET	1 OF 1
DESCRIPTION	PESMA1014-50PK
ITEM NO.	
REV	A

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES	
DIMENSIONS IN [ ] ARE MILLIMETERS	
TOLERANCES:	
X = ± .2 [5]	FRACTIONS
XX = ± .02 [.5]	
XXX = ± .005 [.13]	± .032
	± .0132
	ANGLES ± 1°
CABLE LENGTH TOLERANCES:	
≤ 12 [305] = +1 [25] / -0	
≥ 12 [305] ≤ 60 [1524] = +1 [51] / -0	
> 60 [1524] ≤ 120 [3048] = +4 [102] / -0	
> 120 [3048] ≤ 300 [7620] = +6 [152] / -0	
> 300 [7620] = +5% / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY	
AND SUBJECT TO CHANGE WITHOUT NOTICE.	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.  
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.