

WR-75 Waveguide 20 dB Broadwall Coupler, UG Cover Flange, N-Type Female Coupled Port, 9.84 GHz to 15 GHz, Copper

Waveguide Couplers Technical Data Sheet

PEW75CP001-20

The PEW75CP001-20 is a WR-75 Directional Broadwall waveguide coupler with N female coupled port that operates in the frequency range of 9.84 to 15 GHz. This Waveguide component has a maximum VSWR of 1.25:1. These designs are made of painted copper alloy and incorporate a broad wall configuration that result in a mid-band nominal coupling value of 10, 20, 30, 40 or 50 dB. Common applications for this component would be where power measurements are required within a system for measuring/sampling power or frequency monitoring with minimal signal loss to the main transmission line. Pasternack offers a complete family of waveguide Crossguide and Broadwall couplers that are in-stock and ship same day.

Features

- Three Port Broadwall Waveguide Coupler
- 20±0.7 dB Nominal Coupling Level
- Integrated N Female Connector coupled port
- 9.84 GHz to 15 GHz Frequency Range
- Main Line VSWR < 1.1:1
- Max Power 250W (CW)

Applications

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Electrical Specifications


Description	Minimum	Typical	Maximum	Units
Frequency Range	9.84		15	GHz
Coupler				
Nominal Coupling Level		20		dB
Directivity	35			dB
Insertion Loss			0.2	dB
Main Line VSWR			1.1:1	
Secondary Line VSWR			1.25:1	
Coupling Flatness			±0.7	dB
Input Power (CW)			250	Watts
Input Power, Peak			50	kWatts

Mechanical Specifications

Size

Length	11.81 in [299.97 mm]
Width	1.5 in [38.1 mm]
Height	1.5 in [38.1 mm]
Weight	0.98 lbs [444.52 g]
Flange Type	UG Cover

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-75 Waveguide 20 dB Broadwall Coupler, UG Cover Flange, N-Type Female Coupled Port, 9.84 GHz to 15 GHz, Copper PEW75CP001-20](#)



WR-75 Waveguide 20 dB Broadwall Coupler, UG Cover Flange,
N-Type Female Coupled Port, 9.84 GHz to 15 GHz, Copper

Waveguide Couplers Technical Data Sheet

PEW75CP001-20

Flange Material and Plating
RF Connector Type

Copper, Passivated
N Female

Coupler Body Material and Plating

Copper, Passivated

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

WR-75 Waveguide 20 dB Broadwall Coupler, UG Cover Flange, N-Type Female Coupled Port, 9.84 GHz to 15 GHz, Copper from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-75 Waveguide 20 dB Broadwall Coupler, UG Cover Flange, N-Type Female Coupled Port, 9.84 GHz to 15 GHz, Copper PEW75CP001-20](#)

URL: <https://www.pasternack.com/wr75-waveguide-20db-broadwall-coupler-ug-15mhz-pew75cp001-20-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

WR-75 Waveguide 20 dB Broadwall Coupler, UG Cover Flange,
N-Type Female Coupled Port, 9.84 GHz to 15 GHz, Copper

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/31/2023	HBAKKE	SPONG



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		 		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES: X ± .2 [5] FRACTIONS XX ± .02 [.5] ± 1/32 XXX ± .005 [.13] ANGLES ± 1°		SCALE NONE SHEET 1 OF 1			
CABLE LENGTH TOLERANCES: ≤12 [305] = +.1 [25] / -0 >12 [305] ≤ 60 [1524] = +.2 [51] / -0 >60 [1524] ≤ 120 [3048] = +.4 [102] / -0 >120 [3048] ≤ 300 [7620] = +.6 [152] / -0 >300 [7620] = +.5% / -0		DESCRIPTION WR-75 Waveguide broadband coupler, 20dB with N-type female connector			
Website: www.Pastermack.com Phone: 1.866.727.8376 1.949.261.1920		ITEM NO.		REV	
SIZE		CAGE CODE		DRAWN BY	
A		53919		HBAKKE	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.		PEW75CP001-20		A	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR IN PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.