



WR-28 Waveguide 40 dB Crossguide Coupler, UG Cover Flange, 2.92mm Female Coupled Port, 26.5 GHz to 40 GHz, Brass

Waveguide Couplers Technical Data Sheet

PEWCP1089K-40

The PEWCP1089K-40 is a 40 dB WR-28 three port crossguide coupler with integrated 2.92mm Female connector for the coupled port. This coupler can be mounted directly into the waveguide signal path, connected via coax to allow signal sampling /monitoring. The coupler has a typical VSWR of 1.1:1 and are made of Brass with UG Cover flanges. The PEWCP1089K-40 is part of a family of cross guide couplers offered by Pasternack with coupling values ranging from 20 to 50 dB.

Features

- Three Port Crossguide Waveguide Coupler
- 40 ± 1.5 dB Nominal Coupling Level
- Integrated 2.92mm Female Connector for the coupled port
- 26.5 GHz to 40 GHz Frequency Range
- Low VSWR < 1.5:1

Applications

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	26.5		40	GHz
Coupler				
Nominal Coupling Level		40		dB
Coupling Accuracy			± 1.5	dB
Directivity	15			dB
Insertion Loss		0.2		dB
Main Line VSWR			1.1:1	
Secondary Line VSWR			1.5:1	
Input Power (CW)			200	Watts
Input Power, Peak			20	kWatts

Mechanical Specifications

Size	
Length	1.969 in [50.01 mm]
Width	1.654 in [42.01 mm]
Height	1.27 in [32.26 mm]
Weight	0.11 lbs [49.9 g]
Interface	
Waveguide Size	WR-28

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-28 Waveguide 40 dB Crossguide Coupler, UG Cover Flange, 2.92mm Female Coupled Port, 26.5 GHz to 40 GHz, Brass PEWCP1089K-40](#)

WR-28 Waveguide 40 dB Crossguide Coupler, UG Cover Flange,
2.92mm Female Coupled Port, 26.5 GHz to 40 GHz, Brass



Waveguide Couplers Technical Data Sheet

PEWCP1089K-40

Flange Type

RF Connector Type

Coupler Body Material and Plating

UG Cover

2.92mm Female

Brass Copper, Gold

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

WR-28 Waveguide 40 dB Crossguide Coupler, UG Cover Flange, 2.92mm Female Coupled Port, 26.5 GHz to 40 GHz, Brass from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-28 Waveguide 40 dB Crossguide Coupler, UG Cover Flange, 2.92mm Female Coupled Port, 26.5 GHz to 40 GHz, Brass PEWCP1089K-40](https://www.pasternack.com/40-db-wr-112-waveguide-crossguide-coupler-fmwcp1089K-40-p.aspx)

URL: <https://www.pasternack.com/40-db-wr-112-waveguide-crossguide-coupler-fmwcp1089K-40-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWCP1089K-40 CAD Drawing

WR-28 Waveguide 40 dB Crossguide Coupler, UG Cover Flange,
2.92mm Female Coupled Port, 26.5 GHz to 40 GHz, Brass

