



WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass

Waveguide Accessories Technical Data Sheet

PEWGP1009

Features

- WR-75 Waveguide
- Operating Frequency Range from 9.84 GHz to 15 GHz
- UG Cover and UG Grooved Flanges
- 1.25:1 Max VSWR
- 500 Watts (CW) Max Power Handling
- Insertion loss: 0.25 dB Max
- Thickness: 0.79 inches
- PTFE window material
- Pressure Handling Capability: 29 PSI Max

Applications

- Radar Systems
- Military and Space
- Wireless Radio Systems
- Communication Systems
- R&D Labs
- Microwave Radio Systems

Description

Waveguide pressure windows are used to isolate pressurized components from non-pressurized components within a waveguide system. They can also provide protection against contaminants (debris, moisture and dust) from entering the waveguide system and degrading its RF performance. The PEWGP1009 is a WR-75 waveguide pressure windows that operates in the frequency range of 9.84 GHz to 15 GHz. This WR-75 waveguide termination has a Max VSWR of 1.25:1. This waveguide pressure window is made of annealed copper and incorporates UG Cover and UG Grooved flange interface. Waveguide pressure windows are part of Pasternack's comprehensive waveguide product offerings which are available in stock and ready for same-day shipment.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	9.84		15	GHz
VSWR			1.25:1	
Insertion Loss		0.25		dB
Input Power			500	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass PEW-GP1009](#)



WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass

Waveguide Accessories Technical Data Sheet

PEWGP1009

Mechanical Specifications

Body Material	Copper Brass
Body Finish	Passivation
Length	1.496 in [38][mm]
Width	1.496 in [38][mm]
Height	0.787 in [19.99][mm]
Weight	0.22 lbs [99.79][g]

Compliance Certifications

 (see [product page](#) for current document)

WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass PEWGP1009](#)

URL: <https://www.pasternack.com/pewgp1009-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWGP1009 CAD Drawing

WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass

REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
A	INITIAL RELEASE	15-04-2021	SPOONG	

PRESSURIZING DIRECTION



THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNACK CORPORATION. ALL RIGHTS RESERVED.	
PASTERNACK	an INFINITE brand
Pasterнак Enterprises, Inc.	Pasterнак Enterprises, Inc.
P.O.Box 167659, Irvine, CA 92623.	P.O.Box 167659, Irvine, CA 92623.
Phone: 1.949.261.1920 Fax: 1.866.727.8376	Phone: 1.949.261.1920 Fax: 1.866.727.8376
www.pasternack.com email: sales@pasternack.com	www.pasternack.com email: sales@pasternack.com
SIZE	SCALE
A	N/A
53919	REV
MVEERAPPAN	A

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS
TOLERANCES:
 $X=\pm$ 2 [5.08] FRACTIONS
 $.XX=\pm$.01 [.25] \pm 1/32
 $XXX=\pm$.005 [.13] ANGLES \pm 1°

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.
THIRD-ANGLE PROJECTION

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.
T-Rev. B