



WRD-650 Double Ridge Waveguide 40 dB Loop Coupler, N Female Coupled Port, 6.5 GHz to 18 GHz, Aluminum

Waveguide Couplers Technical Data Sheet

PEWRD650CP04-40

The PEWRD650CP04-40 is a WRD-650 Directional Loop double ridge waveguide coupler with N female coupled port that operates in the frequency range of 6.5 to 18 GHz. This Waveguide component has a maximum VSWR of 1.8:1. These designs are made of painted aluminum and incorporate a Loop configuration that result in a mid-band nominal coupling value of 10, 20, 30, 40 or 50 dB. Common applications for this component would be where power measurements are required within a system for measuring/sampling power or frequency monitoring with minimal signal loss to the main transmission line. Pasternack offers a complete family of waveguide Crossguide, Loop and Broadwall couplers that are in-stock and ship same day.

Features

- Three Port Loop Waveguide Coupler
- 40±2.5 dB Nominal Coupling Level
- Integrated N Female Connector coupled port
- 6.5 GHz to 18 GHz Frequency Range
- Main Line VSWR < 1.15:1
- Max Power 400W (CW)

Applications

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	6.5		18	GHz
Impedance		50		Ohms
Coupler				
Nominal Coupling Level		40		dB
Directivity	10			dB
Insertion Loss			0.3	dB
Main Line VSWR			1.15:1	
Secondary Line VSWR			1.8:1	
Coupling Flatness			±2.5	dB
Input Power (CW)			400	Watts
Input Power, Peak			3	kWatts

Mechanical Specifications

Size

Length	3.94 in [100.08 mm]
Width	1.38 in [35.05 mm]
Height	1.38 in [35.05 mm]
Weight	0.475 lbs [215.46 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WRD-650 Double Ridge Waveguide 40 dB Loop Coupler, N Female Coupled Port, 6.5 GHz to 18 GHz, Aluminum PEWRD650CP04-40](#)



WRD-650 Double Ridge Waveguide 40 dB Loop Coupler,
N Female Coupled Port, 6.5 GHz to 18 GHz, Aluminum

Waveguide Couplers Technical Data Sheet

PEWRD650CP04-40

Interface

Waveguide Size

WRD-650

Flange Type

Cover

RF Connector Type

N Female

Coupler Body Material and Plating

Aluminum, Gray

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



WRD-650 Double Ridge Waveguide 40 dB Loop Coupler, N Female Coupled Port, 6.5 GHz to 18 GHz, Aluminum from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WRD-650 Double Ridge Waveguide 40 dB Loop Coupler, N Female Coupled Port, 6.5 GHz to 18 GHz, Aluminum PEWRD650CP04-40](#)

URL: <https://www.pasternack.com/wrd650-waveguide-40db-broadwall-coupler-18ghz-pewrd650cp04-40-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

WRD-650 Double Ridge Waveguide 40 dB Loop Coupler, N
Female Coupled Port, 6.5 GHz to 18 GHz, Aluminum



FLANGE DETAIL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION

WRD-650 Waveguide Loop Coupler with N-type Female Connector, 40dB Coupling

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
------	-----------	----------	----------	-----

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN () ARE MILLIMETERS

TOLERANCES:

[5] | FRACTIONS

 $\pm 1/32$ 5 [.13] | ANGLES $\pm 1^\circ$

LENGTH TOLERANCES:

 $\leq 12 [305] = +1 [25] / -0$
$$J \leq 60 [1524] = +2 [51] / -0$$
$$\leq 300 [7620] = +6 [152] / -0$$
 $+300 [7620] = +5\% / -0$

THIS ARE FOR REFERENCE ONLY

TO CHANGE WITHOUT NOTICE

3